


# BarcoVision 1609s + Iris<sup>3</sup>



## 技术规格

## BARCOVISION 1609S + IRIS<sup>3</sup>

### 一般规格

#### 兼容性

Horizontal scan frequency of 15-18 kHz, 30-35 kHz and 60-64 kHz autolock  
Standard and S-Video  
Line doubled and line quadrupled Video  
High Definition, extended or improved television Standards  
Compatible with standard and Tri-level sync signals

#### 对比度

>1000:1 (full white/full black)

#### 光输出

1600 Lumen at 10 % peak white  
210 ANSI Lumen (Economy mode)  
270 ANSI Lumen (Normal mode)  
310 ANSI Lumen (Boost mode)

#### 屏幕尺寸

Min.: 2 m (6.6 ft)  
Max.: 6.6 m (22 ft)

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看[www.barco.com.cn](http://www.barco.com.cn)以了解最新规格。