

# EC-30

Small event controller



- Specifically designed for small events
- Full show control at your fingertips
- Instant access to crucial functionalities

The most compact version of the Event Master controllers delivers instant access to the most crucial features, for everything from a tradeshow booth to a large corporate event, or even a music tour. The EC-30 gives the operator a compact surface and simplified workflow, while still providing fingertip control where budget and space are the deciding factors. The EC-30 is an extension of the Event Master toolset, bringing the essential selections for sources, presets, layers and destinations to your fingertips. As a USB peripheral added to your existing Event Master control computer, it is the most cost-effective and compact alternative to a full-sized controller.

## EC-30

- Complimentary control of the Event Master Series switchers
- High resolution T-Bar
- 4 user-programmable buttons with customizable LCD displays
- Dedicated Background layer button
- 8 dedicated Layer selection buttons with multi-page functionality
- Dedicated layer function buttons for transitions, freeze, and FX arming
- 12 user-definable Destination buttons with multi-page functionality
- USB port for connection to host computer
- Status LEDs and color coded LCD displays
- Auto-ranging 12v 2.08a power supply (100-250VAC)
- 2 user-assignable custom function buttons

**Product specifications****EC-30**

General specifications	
Connectivity	USB connection from Event Master Toolset host computer (OSX or Windows 7 and higher)
Dimensions (HxWxD)	105.4 x 465.6 x 321 mm (4.15 x 18.33 x 12.63 inches)
Weight	3.18 kg (7 lbs)

Last updated: 22 Jun 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.