

# H 2.0 Quad output card



- Four HDMI™ 2.0 connectors
- Supports up to 4x 1600p@60, or 2x 4K@60p/ UHD per card (single cable)
- HDCP 2.2 compliant
- Support for VESA/CEA, and custom timings
- Automatic output acquisition and configuration

**Product specifications****H 2.0 QUAD OUTPUT CARD****General specifications**

Connectors	4x full sized HDMI™ connectors
Resolution	up to 2x 4096x2160@60p
Color depth	8-bit; 10-bit; 12-bit (DL or lower)
Features	Rotation and splitter mode
Color sampling	up to UHD@60p 4:4:4 8-bit, or 4:2:2 10-bit
HDCP	HDCP 2.2 compliant
Signal capacity	600 MHz

**Specifications when used with Encore3**

Connectors*	4x full sized HDMI™ 2.0 connectors
Resolution*	Support up to 4x 4096x2160 @60Hz
Color depth*	8-bit; 10-bit; 12-bit
Color sampling*	up to UHD@60p 8-bit 4:4:4 or 10-bit 4:2:2
HDCP*	HDCP 2.2 compliant
Signal capacity*	up to 4096x2160 @60Hz
*	Specification when used with Encore3

Last updated: 23 Dec 2025

© 2025 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.