

# WSG-110

Small form factor thin client for SecureStream



**Barco's WSG-110 thin client is a small form factor to display encoded streams coming from an IP network. It supports standard H.264, Barco's low-latency Video2Data (V2D), Barco ProServer/Virtual Network Computing (VNC) and Remote Display Protocol (RDP) decoding.**

## **Low noise thin client for up to two displays**

The WSG-110 is designed and fully qualified for Barco's SecureStream solution. Once connected to a SecureStream system, the pre-configured appliance enables customers to capture networked source information from anywhere. It displays these sources with a user-friendly user interface.

Multiple appliances can be combined to show sources as part of a composed desktop on monitors of an OpSpace workstation, a truly unified workspace for mission-critical applications.

This thin client can process up to eight HD-quality sources and allows organizing visual and interactive content as a smart multi-viewer to enhance knowledge and improve decision-making.

## **Features**

- Pre-configured thin client for SecureStream
- Linux based operating system
- Intel® i7 Quad Core™ processor for low-latency application processing and software based media decoding

- Processes up to eight HD sources
- Universal IP streaming video decoding (H.264, V2D, ProServer/VNC, RDP)
- Silent operation
- Small form factor
- Flexible mounting options

**技術仕様****WSG-110**

一般仕様	
プラットフォーム	SecureStream
プロセッサ	Intel(R) Core(TM) i7 Quad core CPU 3.4GHz
メモリー	8 GB RAM
ハードディスク	128 GB SSD
ネットワーク	2x 1Gb/s LAN
グラフィックカード	Intel HD Graphics 630
出力	Up to 2x displays HD 1920x1200 @60Hz via DisplayPort (HDMI via included adapters)
入力	IP video sources (H.264), Video2Data (Barco V2D), Virtual Network Computing (VNC), Remote Desktop Protocol (RDP)
フォーム・ファクタ	60 x 190 x 190 mm   2.36 x 7.48 x 7.48 in Packed: 230 x 260 x 308 mm   9.06 x 10.24 x 12.13 in
重量	2.2kg Packed: 4.5kg
電源	External PSU 150W / 90 – 264 VAC / 47 – 63 Hz
消費電力	Typ. 83W   max. 110W
適用温度範囲	0° -40° C   32° -104° F
湿度	Max. 80% (non-condensing)
MTBF	47,500 h
ノイズレベル	Max. 32dbA (measured at 1m/32.8ft distance at 22°C/72°F)
適合性	CE, CB, UL, RCM, BIS, CU-EAC, FCC Class A CCC contact Barco Sales
マウント	Order no. R9811098 P110 VESA Mount (for 1x OPS-110 + 1x PSU) R9811099 P110 Rack Mount (for 2x OPS-110 + 2x PSU)

生成日:14 Jul 2023

技術仕様は予告なく変更する場合があります。最新情報については、[www.barco.com](http://www.barco.com) をご覧ください。