


Single mode fiberlink

Adds fiber-optic technology to the solution for guaranteed quality of the final picture with a reach upto 10 kilometer.



Product specifications**SINGLE MODE FIBERLINK****General specifications**

Reach	10 kilometer cascable
Signal	1,5 Gig/sec, no compression full quality stream to daylight display Proprietary transmission error detection and correction protocol
Outdoor Compliance	IP 65 fiberoptic connectors

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.