

DP-3000

2K Digital cinema projector for screens up to 30m (98ft)



Product specificaties**DP-3000****General specifications**

Digital MicroMirror Device™	3 x 1.2" DC2K dark metal devices
Contrastverhouding	2000:1
Native resolutie	2048 x 1080
Behuizing	Hermetically sealed DMD™ and optical assembly
Schermbreedte	Screen width (screen gain 1:8) @ 14ftL * : 30m -100ft Screen width (screen gain 1:3) @ 14ftL * : 25m -83ft (*) = +/-10 variation possible between units
Montage	universal pedestal (optional)
Omgevingstemperatuur	max. 35°C / 95°F
Lamp	1.5kW -7kW Xenon lamp size Lamp power: 1.5kW -7kW
Digitale video-ingangen	2 x SMPTE 292M inputs 2 x DVI input both selectable as single or as dual link
Primelenzen	Prime lens (1.4 - 2.05) 1.2" DC2K Prime lens (1.6 -2.35) 1.2" DC2K Prime lens (1.8 -2.8) 1.2" DC2K Prime lens (2.15 - 3.6) 1.2" DC2K Prime lens (2.8 - 5.5) 1.2" DC2K
Projectordiagnose	via PC touch panel via Communicator control software via SNMP agent
Voedingsvereisten	3 x 400V + N or 3 x 220V 30.000 BTU / hr (with 6.5kW lamp)
Afmetingen	Projector head: 640(H) x 730(W) x 1170(D) mm 24.2(H) x 28.7(W) x 46.1(D) inch Powerbox: 450(H) x 329.5(W) x 473.7(D) mm 17.7(H) x 13.0(W) x 18.6(D) inch
Gewicht	projector: 125kg (275lbs) powerbox: 30kg (66lbs)
Opties	CLO-constant light output anamorphic lens fitting (1.25 x) ACS-2048 SNMP agent motorized/memorized lens focus, zoom & shift
Bestelgegevens	R9004480

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.