

LD (2.5-4.0:1)



Product specifications**LD (2.5-4.0:1)****General specifications**

Motorized Zoom	Yes Zoomring required to activate motorisation See 'options'
Motorized Focus	Yes Adapter ring required to mount the lens See 'options'
Throw Ratio	On ELM G10: 2.5 -4.0 : 1 On ELM R12: 2.0 -3.2 : 1
Lens Shift Horizontal	On ELM G10: Left 70% 70% Right On ELM R12/18: Left 25% 25% Right
Lens Shift Vertical	On ELM G10: Up 105% 105% Down On ELM R12/18: Up 35% 35% Down

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.