



MDSC-8532 SSTF / NXF

4K UHD surgical display



- **Optimized for endoscopy and surgical imaging**
- **Bright and crisp color video images**
- **Billions of true-to-life colors**
- **Accurate color-calibration s**
- **Fast power on and automatic failover**
- **'A' ecolabel for a sustainable choice**

See more with surgical 4K precision, with our 32", A-ecolabel endoscopic and surgical display. This 4K UHD display offers exceptional brightness, crisp contrast, and vivid color video images, important where morphology is inconspicuous or recessed.

Uncompromising image quality

See more subtle differences with the MDSC-8532's 4K resolution. The wide color gamut and Barco's industry-leading calibration provide a full range of true-to-life colors. And ultra-low latency ensures real-time feedback for perfect hand-eye coordination.

Fast and efficient


The MDSC-8532 is low in weight and slim in design. Its dual user interface – there is one at the front and one at the back – accommodates individual user preferences. The display is fast to power-up, low in energy consumption, and features an automatic failover.

Easily set up and change the display's layout configurations to fit your procedure. And increase efficiency with customizable shortcut buttons.

User centric design

The slim lightweight modern design features an optimized full-front glass design with bezel protection on all sides safeguards against damage by surgical lights and IV poles. It also protects the display from surgical fluids and contaminants.

The fanless design (SSTF version) and intelligent cable cover support infection control, disinfection, and cleaning. The MDSC-8532 is approved for use in the



vicinity of patients and includes an automated failover method.

It is fast to power-up and features an automatic failover. A dual interface design (front and back) accommodates individual user preference while customizable shortcuts enable faster user interactions.

The MDSC-8532 comes with a 3-year warranty and the possibility to extend this to 5, with our EssentialCare package..

Models

- MDSC-8532 SSTF: 32" 4K display with SSTP DisplayPort connectivity and fanless design, white version
- MDSC-8532 NXF: 32" 4K display with SSTP DisplayPort connectivity, fanless design and integrated Barco Nexxis Decoder, white version

Product specifications**MDSC-8532 SSTF / NXF**

General specifications	
Screen technology	TFT AM LCD / LED backlight
Active screen size (diagonal)	32" (813 mm)
Active screen size (H x V)	708 x 399 mm
Aspect ratio	16:9
Brightness	Native: 850 cd/m ² (typical) Default setting: 550 cd/ m ² stabilized @6500K & Native color space
Resolution	3840 x 2160 pixels
Pixel pitch	0.1845 mm
Color support	1 billion (10 bit color depth)
Color gamut	Native: 94% NTSC
Color calibration	ITU-709, DCI-P3, BT.2020 (BT.2020 reproducible colors are within the limit of the LCD panel)
Viewing angle	178° Hor / 178° Ver
Contrast ratio	1350:1 (Typical)
Response time	T _{on} + T _{off} = 18 msec (typical)
White point	Calibrated: 5600K, 6500K, 7600K, 9300K
Electro-Optical Transfer Function (EOTF)	Native, 1.8, 2.0, 2.2, 2.4, Video1, Video2, DICOM (review level)
Front protection screen	2-side anti-reflective alkali-aluminosilicate glass with anti-fingerprint coating
Keyboard	Front: 5-key capacitive touch -user programmable Rear: 5-key membrane
Video inputs	<p>MDSC-8532 SSTF</p> <p>4K-UHD input:</p> <ul style="list-style-type: none"> ■ 1x DP 1.2 SST / MST up to 3840 x 2160 @ 50/60 Hz (user configurable) ■ 2x HDMI 2.0 up to 3840 x 2160 @ 50/60 Hz <p>FHD input (upscaled to UHD):</p> <ul style="list-style-type: none"> ■ 1x DVI ■ 1x 3G-SDI; ■ Note: DP, HDMI and DVI all suport HDCP 1.4 <p>MDSC-8532 NXF</p> <p>4K-UHD input:</p> <ul style="list-style-type: none"> ■ 1x DP 1.2 SST / MST up to 3840 x 2160 @ 50/60 Hz (user configurable) ■ 1x HDMI 2.0 up to 3840 x 2160 @ 50/60 Hz <p>FHD input (upscaled to UHD):</p> <ul style="list-style-type: none"> ■ 1x DVI ■ 1x 3G-SDI; <p>· 2x FO SFP+ for 4K-UHD Nexxis link · Note: DP, HDMI and DVI all support HDCP 1.4</p>
Video outputs	<p>MDSC-8532 SSTF and NXF</p> <ul style="list-style-type: none"> ■ 1x DP 1.2 SST (main input copy) ■ 1x 3G-SDI (loop-through)
Other connectivity	<p>USB-A (Field FW update with USB stick)</p> <p>USB-B (remote control serial protocol)</p> <p>2x 3.5 mm minijack audio/trigger (NXF version only)</p> <p>2x USB-A keyboard/mouse (NXF version only)</p>
Features	User-programmable function keys, Picture-in-Picture, Picture-by-Picture, Image Mirror and Rotation, Zoom, Pan, Failover mode, User profiles, High quality upscaling from SD / FHD input to UHD, FW upload from memory stick

Product specifications**MDSC-8532 SSTF / NXF**

Power consumption	MDSC-8532 SSTF Max. 100W / 25V ± 10% Low power mode: MDSC-8532 NXF Max. 110W / 25V ± 10% Low power mode:
External power supply	AC input: 100 – 240 VAC / 47-63 Hz auto-switch DC output: +25 VDC / 8 A Dimensions: 204 x 81 x 43 mm (8.0 x 3.2 x 1.7") Weight: 0.9 kg (2 lbs)
DC power output	DP connector: +3.3 V / 500 mA USB connector: +5 V / 1 A
Dimensions (W x H x D)	768 x 480 x 79 mm (30.2 x 18.9 x 3.1")
Dimensions packaged (W x H x D)	900 x 720 x 170 mm (35.4 x 28.3 x 6.7")
Net weight display	SSTF: 12.0 kg (26.5 lbs) NXF: 12.7 kg (28 lbs)
Net weight packaged	SSTF: 19.0 kg (41.9 lbs) NXF: 19.3 kg (42.6 lbs)
Mounting standard	VESA 100 x 100 mm
Operating temperature	0°C to 35 °C for performance 0 °C to 40 °C for safety
Storage temperature	-20 °C to 60 °C
Operating humidity	20% to 85% (non-condensing)
Storage humidity	10% to 85% (non-condensing)
Operating altitude	3000 m max. / 70 kPa
Storage altitude	5500 m max. / 50 kPa
Certifications	<ul style="list-style-type: none">■ Approvals/Marking:■ CE (Medical Device Class I), c-UL-us, DEMKO, CCC, BIS, INMETRO■ Green compliance: ROHS-3, REACH, WEEE■ ANSI/AAMI ES 60601-1:2005/(R)2012■ CAN/CSA-C22.2 No. 60601-1: 14■ IEC 60601-1: 2012 Edition 3.1■ EN 60601-1: 2006 + A1:2013 + A12:2014■ IEC 60601-1-2: 2014 + A1:2020■ EN 60601-1-2: 2015 + A1:2021■ FCC CFR 47 Part 15 Subpart B (Class B)■ ICES-003 (Class B)■ GB17625.1-2012; GB4943.1-2011; GB/T9254-2008■ IS 13252(Part 1):2010/ IEC 60950-1 : 2005■ UL 60950-1, 2nd Edition (to make the equivalence with NOM-019)■ ABNT NBR IEC 60601-1:2010 + Emenda 1:2016■ ABNT NBR IEC 60601-1-2:2017■ ABNT NBR IEC 60601-1-6:2011 + Emenda 1:2020■ ABNT NBR IEC 60601-1-9:2010 + Emenda 1:2014
Protection rating	IP21 (IP45 front side only)
Warranty	3 years

Last updated: 12 Sep 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.