

DP2K-P

2K digital postproduction projector



- Improved contrast
- Expanded color gamut
- Superior brightness uniformity

The Barco DP2K-P is a 2K digital projector specifically designed to meet the high-performance needs of the post-production industry.

Proven platform

The DP2K-P builds on the proven platform of the Barco DP2K-B projectors, from which it inherits widely acclaimed benefits such as best-in-class light efficiency, lowest cost of ownership, and ultimate ease-of-use.

Enhanced image detail

To respond to the highly specialized needs of post-production houses, the DP2K-P projector delivers improved contrast, superior brightness uniformity, and a greatly expanded color gamut -considerably wider than the current DCI recommended color space.

Increased control

What's more, the DP2K-P post-production projector is bundled with a special version of the Barco Communicator software, enabling you to fully customize your 2D and 3D look-up tables. This dedicated software provides increased control over the color space, which allows you to do your job with an unprecedented level of accuracy.

- Superior brightness uniformity
- Extra wide color gamut - significantly wider than the DCI recommended color space
- Increased detail thanks to exceptionally high contrast ratio
- Customizable 2D and 3D look-up tables via Communicator software

- Long-term image quality and brightness thanks to proprietary sealed engine and advanced DMD cooling
- Easy to use thanks to the intuitive user interface
- Easy installation and maintenance thanks to proven modular design
- Lowest cost of ownership thanks to lowest lamp operating cost, reusable filters and modular design
- Next-generation electronics ready for DLP Cinema® Enhanced 4K

Product specificaties

DP2K-P

General specifications	
Digital MicroMirror Device™	3 x 1.2" DC2K dark metal devices Advanced DLP Cinema™ signal processing with built-in 3D look-up table
Native resolutie	2,048 x 1,080 pixels
Behuizing	Hermetically sealed DMD and optical assembly
Lamp	1.2kW -4.0kW (Xenon lamp) Compatible with models from all major brands
Lichtuitvoer	5,400 lumens (standard 2kW lamp, 10% deviation possible)
Schermmaat	Up to 7.5 m (24.6 ft) (@ 16 fti (unity gain))
Uniformiteit	Meets the DCI review room specifications (10% deviation possible)
Contrastverhouding	2,500:1
Digitale video-ingangen	2 x SMPTE 292M inputs 2 x DVI input both selectable as single and dual link
I/O-controle	Ethernet 8x GPIO Serial RS232
Primelenzen	1.25 -1.45 1.4 -2.05 1.6 -2.35 1.8 -2.8 2.15 -3.6 2.8 -5.5
Kleurenspectrum	native red: x = 0.7; y = 0.3 native green: x = 0.2; y = 0.76 native blue: x = 0.145; y = 0.04
Voedingsvereisten	220V
Afmetingen	604(H) x 754(W) x 1129(D) mm 23.78(H) x 29.69(W) x 44.45(D) inch NB: min. 5 cm of air inlet spacing required at the bottom of projector
Gewicht	133 kg (293 lbs)
Omgevingstemperatuur	35°C / 95°F
Opties	ACS-2048 3D add-ons Touch panel Pedestal

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

