

ILite 12

12mm, indoor, SMD, 2000 Nit, LED display solution.



Product specifications**ILITE 12****General specifications**

Brightness	2.500 NIT
Calibrated Brightness	2.000+ NIT
Contrast ratio	950 : 1 (500 lux) 1.625 : 1 (225 lux)
Visual Resolution	12 mm
Hor. viewing angle	> 145°
Vert. viewing angle	> 145°
Tile dimensions	Width: 0,448 m Height: 0,448 m Depth: 0,1495 m
Weight	13 kg
Avg Power Consumption	100 W / tile
Max. power consumption	400 W / tile
Temperature range	operating: 0°C <> 40°C storage: -20°C <> 60°C
Screen size	Unlimited
Lifetime	45.000h (half brightness)
Processing	+ 13 bit
Source compatibility	S-Video -Composite -YUV -RGB -SDI -HDSDI -Data DVI up to UXGA

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.