

# MNA-440 DEC -H

HD AV-to-IP adapter for the OR and hybrid OR with HDMITM technology



- **IP-to-AV conversion**
- **Up to 4K resolution**
- **Medical-grade**
- **Established 3rd generation technology**

## **Adapter for the operating room**

The MNA-440 DEC -H with HDMITM technology converts uncompressed IP video streams to HDMI 2.0 video. Other non-video signals such as audio and USB for keyboard/mouse are also supported. End-to-end video latency is amazingly low and is guaranteed not to exceed a single frame.

## **Capabilities**

The MNA-440 adapters are part of Barco's Nexxis solution, which provides users with uncompromised networked visualization for the digital operating room. The compact Nexxis AV-to-IP adapters offer simplicity and flexibility while maintaining the highest possible performance standards and fitness for use in demanding medical environments.

As a third generation device, the MNA-440 DEC -H with HDMITM technology provides the full richness of the established Nexxis platform while:

- increasing future scalability
- improving ease of installation
- adding increased security performance
- reducing ecological footprint

## Product specifications

## MNA-440 DEC -H

General specifications	
Video conversion	Converts uncompressed IP-streams into Digital video signals.
Processing	4096x2160@60Hz on a single output channel  Or 1920x1200@60 on each of the two output channels
Color depth	RGB 8-bit
3D technology	Show one view of the 3D video flow (left eye) on a 2D display
Latency	End-to-end: genlocked subframe; not genlocked one frame.
Security	Decryption of AES 128 encrypted video, data & control signals
Video Output	2x HDMI 2.0 lockable connector
IP connectivity	2x 10GbE Fiber Optic Interface with SFP+ module
IP standards	Zeroconf, IPv4, IGMP, DHCP, RTP, RTCP, 802.1q, AES 128b, HTTP(s)
USB	2x USB Type A
Audio	Stereo line in and Headset/Stereo line out 15mm length compatible 3.5mm TRRS jack
GPIO	1x GPI + 1x camera trigger via 15mm length compatible 3.5mm TRRS jack
Nexxis integration	Supported from Nexxis 1.14 onwards, compatible with MNA-1x0, MNA-240 and MNA-4x0 devices
PSU	External 12VDC Medical Approved PSU, 100-240VAC 50-60Hz 60W with lockable connector at DC side
Power consumption	Maximum: 25W Typical: 17W
Size	35 mm H x 103 mm W x 131 mm D   1.4" H x 4.1" W x 5.2" D (+/-2 mm / 0.1")
Weight	0.4 kg (0.88 lbs)
Temperature	5°C to 40°C (41°F to 104°F)
Humidity	Maximum 85%
Storage	Storage temperature: -20°C to 60°C (-4°F to 140°F) Storage Relative Humidity: 10% to 93%
Acoustic Noise	Typical 32dBA at 20°C at 1m
Mounting	Versatile mounting bracket included
Certifications	<ul style="list-style-type: none"><li>■ CB (IEC 60601-1) Informative report</li><li>■ CB (IEC 60950-1)</li><li>■ cRU, RU (cRUus)</li><li>■ Demko</li><li>■ CE medical device class I</li><li>■ UKCA</li><li>■ BIS Registration, IS 13252 (part 1)</li><li>■ KC</li><li>■ BSMI</li><li>■ RCM</li><li>■ EAC</li></ul>
Standards	Medical Equipment: <ul style="list-style-type: none"><li>■ IEC 60601-1:2005 + Am1:2012</li><li>■ IEC 60601-1-6:2010 + Am1:2013</li><li>■ IEC 60601-1-2:2014 (ed4)</li><li>■ ANSI/AAMI ES 60601-1: A1:2012 + C1:2009/(R)2012 + A2:2010/(R)2012</li><li>■ CAN/CSA-C22.2 No.60601-1:14</li><li>■ EN 60601-1:2006 + A1:2013 + A12:2014</li><li>■ EN 60601-1-6:2010 + A1:2015</li><li>■ EN 60601-1-2:2015 (ed4)</li><li>■ FCC class B</li><li>■ ICES-001 Level B</li></ul> ITE Equipment: <ul style="list-style-type: none"><li>■ IEC 60950-1:2005 + Am1:2009 + Am2:2013</li><li>■ EN 60950-1:2006 + A11:2009 + A1:2010 + A12:2011</li><li>■ IS 13252</li></ul>

Last updated: 29 Apr 2024

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.