

ClickShare Bar Pro

Premium video bar for engaging, effortless wireless conferencing



- **Crystal-clear, high-quality stereo audio***
- **Advanced AI-powered 4K camera**
- **Wired roomdock for 4K content sharing and alternative connectivity***
- **Advanced interactivity: touchback, annotation and blackboarding**
- **Carbon-neutral product****

ClickShare Bar Pro is a premium, carbon-neutral, all-in-one video bar that enables engaging, effortless wireless conferencing in medium-sized meeting rooms with any videoconferencing platform. Thanks to its advanced AV capabilities (dual screen*, 4K content sharing) and interactive features (touchback, annotation, blackboarding), it enables crystal-clear audio, sharp views and enhanced interactivity for meetings where all participants feel heard and seen. This solution offers unparalleled flexibility, allowing IT Managers to easily equip their meeting rooms. Paired with a 5-year warranty, the bar overall reduces the Total Cost of Ownership by consolidating all collaboration, audio and video functionalities into one powerful device.

*Stereo speakers, dual screen and wired fallback will be available mid 2024.**Carbon-neutral label targeted for end Q1 2024.

Product specifications**CLICKSHARE BAR PRO**

General specifications	
Operating system	Windows 10 and higher macOS 11 (Ventura) and higher Android v13 and higher (ClickShare App) iOS 16 and higher (ClickShare App)
System requirements	For a smooth experience with Microsoft Teams or Zoom Minimum: Intel i3 dual-core processor / 8GB RAM / OS: Windows 10 latest build or Mac OS Ventura latest build Recommended: Intel i5 4-core processor / 8GB RAM / OS: Windows 11 latest build or Mac OS latest build
Video outputs	4K UHD (3840*2160) @ 30Hz. or 2x 1080p @ 30Hz. HDMI 1.4b or 1.4b or USB-C DP ALT mode (DisplayPort 1.2) (Dual screen available mid 2024)
Video inputs	4k UHD (3840*2160) @30Hz.USB-C DP ALT mode (DisplayPort 1.2)
Camera	4K, 1080p, 720p at 30fps, 3x zoom/ePTZ, 120°FOV
Camera AI	Group framing, speaker framing and tracking and composition mode with up to 4 people
Audio output	2x 10W full duplex and stereo speakers, 8 Ohms impedance (available mid 2024)
Audio pickup	6 beamforming MEMS microphones with echo and background noise cancellation. Pickup range up to 15 feet / 4.5 meters
ClickShare Buttons	2
ClickShare App	Desktop & Mobile
Native protocols	Airplay, Google Cast, Miracast (available mid 2024)
Noise Level	Fanless
Authentication protocol	WPA2-PSK in stand-alone mode WPA2-PSK or IEEE 802.1X using the ClickShare Button in network integration mode
Wireless transmission protocol	IEEE 802.11 a/g/n/ac and IEEE 802.15.1
Reach	Max. 30m (100 ft) between ClickShare Button and ClickShare Bar
Frequency band	2.4 GHz and 5 GHz (DFS channels supported in select number of countries in network integration mode)
Connections	1x USB-C 3.1 (DP) to screen,1x USB-C 3.1 (DP) video input, 1x USB-A 2.0, 1x Ethernet LAN 1Gbit, 1x USB-C 2.0 (side)
Temperature range	Operating: 0°C to +40°C (+32°F to +104°F) Max: 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	Kensington lock (back and bottom)
Certifications	FCC/CE
Touch screen support & Interactivity	Yes
Wireless conferencing	via App or Button
Local view	Yes
Network connection	LAN & WiFi
Management and reporting	Yes
Warranty	1 year standard. 5 years coverage upon registering via SmartCare
ClickShare Base Unit dimensions	
Dimensions (HxWxD)	98 mm x 640 mm x 101 mm
Power consumption	Operational: 5-20W, 65W Max
Power supply	Standard 110/220 V AC plug or USB-C (back)
Weight	2500 gr

Last updated: 12 Apr 2024

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.