

ClickShare CSM-1

Wireless presentation system - Barco ClickShare - CSM-1



ClickShare is Barco's wireless presentation and collaboration system, that allows any meeting participant to share content on the central meeting room screen.

An unmatched user experience

At the click of a button, the content of your laptop, tablet or smartphone is displayed on the large screen. The result is that all participants are involved more intensely in the decision-making process. Coupling extreme simplicity with an unmatched user experience, everybody who has used ClickShare is immediately hooked. The system's stability and ease-of-use, also drastically limits the number of needed interventions by the IT department.

Instantly on screen, using any device

A ClickShare CSM-1 set consists of two USB-powered devices, ClickShare Buttons, and a Base Unit. The Base Unit has a fixed connection to the meeting room's visualization system, and takes care of all the needed processing. Users who want to get their presentation on the large meeting room screen, simply connect a Button to their PC or MAC. They start the application, click the ClickShare Button and immediately their desktop is wirelessly transferred to the large visualization system. Alternatively, when using a smartphone or tablet (either iOS or Android-powered), a simple app allows you to share content as well. A maximum of two people can show their content on-screen simultaneously.

Product specifications**CLICKSHARE CSM-1**

ClickShare Base Unit dimensions	
Weight	530g / 1.17lbs (incl. antennas)
Dimensions (HxWxD)	Excl. antennas: 37mm x 186mm x 85mm / 1.457" x 7.323" x 3.346" Incl. antennas: 125mm x 186mm x 121mm x / 4.921" x 7.323" x 4.763"
Power consumption	Standby 3.5 W Operation typical: 6W Maximum: 7.5 – 9.7W
General specifications	
AirPlay Support	iOS mirroring (AirPlay) from iOS 9.0 up to iOS 10.2 / macOS 10.11 El Capitan
Google Cast Support	Google Cast not supported
Operating system	Windows 7/8/8.1/10 32 & 64 bit macOS 10.10/10.11/10.12 (Sierra) Android v5 & v6 (ClickShare app) iOS 8 & 9 (ClickShare app)
Video outputs	HDMI (video and audio), 15-pin VGA
Frame rate	Up to 30 fps depending on environment
Output resolution	HDMI: 1280x720 (720P), 1920x1080 (1080p) VGA: SVGA (800x600) / XGA (1024x768) / WXGA(1280x768) / WXGA+(1280x800) / 1360 * 768 / 1440 * 900
Number of sources simultaneous on screen	2 (2 via Buttons, 1 from mobile device)
Number of simultaneous connections	8
Audio	Radio quality 16bits 22KHz (no synchronization) via audio jack or HDMI
iPad, iPhone and Android compatibility	Available via ClickShare Presenter app for static content.
Extended desktop	Available (depending on the driver of your graphics card)
Authentication protocol	WPA2-PSK
Wireless transmission protocol	IEEE 802.11 a/b/g/n
Data rate wireless	Up to 300Mbps
Reach	Max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit
Frequency band	2.4 GHz and 5 GHz (DFS channels not supported)
Power	External Power adaptor 5V DC input 2.6A (included in set)
Connections	USB Host x 2 RJ-45 LAN Port Audio analog line out on mini jack socket (3.5mm)
Temperature range	Operating: 0°C to +40°C (+32°F to +104°F) Storage: -10°C to +60°C (+14°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 80% relative humidity, non-condensing
Wall mounts	Included in set
Certifications	FCC/CE
Warranty	3 years standard Possible to extend to 5 years

Last updated: 15 Mar 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.