

CRWQ-72B

7,000 lumens, WQXGA, single-chip DLP projector



- **Razor-sharp images with vibrant colors**
- **Large lens shift range for flexible installation**
- **Compact design**
- **24/7 reliability**

***Only available at selected distributors**

What's more, the CRWQ-72B replaces complex setups with multiple displays to get a high-resolution display in your meeting room, collaboration room or visualization room.

High-contrast images

The CRWQ-72B projector combines a unique WQXGA (2,560 x 1,600) resolution - much higher than any other single-chip DLP projector - with a light output of 7,000 lumens. The projector enables showing more data on screen simultaneously which has a documented effect on work efficiency, because more pixels equal more information that can be shown.* As it provides stable and high-contrast images that allow you to concentrate better and offers a low noise level, you can turn your meeting room into an efficient collaboration room.

Flexible installation

Next to having the smallest installation footprint, the CRWQ-72B is also the lightest projector in the 6,500 to 10,000 lumens segment. Thanks to its range of all-glass and high-quality lenses with wide lens shift, it offers ultimate installation flexibility.

Built to last

The CRWQ-72B features a filter-free design and reliable DLP® technology for unmatched picture accuracy and low total cost of ownership. Designed for unlimited use, it also comes with a three-year warranty, for true peace of mind.

Product specificaties

CRWQ-72B

General specifications	
Type projector	single-chip DLP projector
Technologie	LVDC DMD™ with DarkChip3™
Resolutie	2,560 x 1,600 (WQXGA)
Helderheid	7,000 ANSI lumens
Contrastverhouding	6,500:1
Helderheidsuniformiteit	>90%
Beeldverhouding	16:10
Type lens	All glass lenses
Lenzen	wide angle lens EN42 (0.8:1), ultra wide zoom lens EN46 (0.8-1.21:1), wide angle lens EN43 (1.2-1.7:1), standard zoom EN41 (1.7-2.5:1), long throw zoom EN44 (2.50-4.60 :1), ultra wide fixed EN47 (0.65 : 1)
Optische lensverschuiving	Vertical: -144% to +144%; Horizontal: -70% to +70% (on zoom lenses)
Kleurcorrectie	RealColor™
Lampen	2 x 300W UHP Vidi
Levensduur lamp	Up to 2,000 hours (full power) / Up to 2,500 hours (eco mode)
Lampbehuizing, snelle vervanging	yes
Lampgarantie	500 hours or 90 days
Verzegelde DLP™-kern	Yes
Oriëntatie	table -ceiling
Ingangen	2 x DVI-I; 2 x HDMI 1.3a; 2 x VGA; Video inputs; 1 x component; 1 x S-video
Invoerresoluties	Up to 2,560 x 1,600 pixels input on all models. Output resolution depends on native resolution; HDTV (1080p, 1080i, 720p); EDTV (576p, 480p); SDTV (576i, 480i); NTSC, PAL, SECAM; progressive scan
Software tools	Projector Toolset, ProNet
Controle	1 x RJ-45 TCP/IP; 1 x 9-pin D-SUB RS232; 2 x 12V programmable trigger (3.5mm mini jack); 1 x Wired Remote 3.5mm mini jack; 2 x USB
Netwerkverbinding	10/100 base-T, RJ-45 connection
Voedingsvereisten	100-240V / 50-60Hz
Energieverbruik	912W
Geluidsniveau	34 dB
Operationele omgevingstemperatuur	10-40°C / 50°-104°F
Operationele vochtigheid	20-80% RH
Dissipatie BTU	max 3,109 BTU/h
Afmetingen (B x L x H)	510 x 376 x 233 mm / 20.08 x 14.80 x 9.17 inches
Gewicht	12.7 kg (28.0 lbs)
Standaardaccessoires	Power cord, wireless remote control
Certificeringen	Compliant with FCC, part 15 Class A and CCC, cCSAus, cUL, UL and CE
Garantie	Limited 3 years parts and labor. Extendable up to 5.

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

