

XLM H25

The ultimate high-brightness projector



Barco's XLM H25 projector is the ultimate high-brightness projector available on the market today. As the first DLPTM projector with a native wide-screen aspect ratio, native 2048 x 1080 resolution and light output of 28 000 center lumen, the XLM H25 projector is ideally suited to ultra wide-screen projections.

With its functional design, fully sealed DMD engine and adjustable convergence system, the XLM H25 projector is purpose built to work around the clock, making it ideal for use in the demanding rental & staging and large events markets.

Product specificaties**XLM H25**

General specifications	
Lichtuitvoer	28000 Center Lumen
Resolutie	2048 x 1080 (native)
Helderheidsuniformiteit	> 80% for the total screen
Contrastverhouding	1600 : 1 (full field) High contrast mode: Available with special lenses
Beeldscherm	3 Chip DLP DC2K (resolution of 2048 x 1080 pixels (aspect ratio 1.89:1)).
Kenmerken	<ul style="list-style-type: none"> ■ Advanced multi windowing ■ Seamless switching with effects ■ Standard light shutter ■ Rigging point ■ Carrying handle ■ Electronic tilt ■ High contrast mode ■ P7 color processing
Picture-in-Picture	Up to 4 sources simultaneous (with alpha blending; z-order)
Ingangen	Modular inputs Standard: <ul style="list-style-type: none"> ■ 1x DVI ■ 1x SDI ■ 1x HD-SDI (all + loop through) ■ 1x RGB Analogue (up to UXGA) Optional: <ul style="list-style-type: none"> ■ 1x composite video/S-Video ■ 1x RGB/YUV (both + loop through)
Uitgangen	DB15 out (2048 x 1080 50/60 HZ)
Communicatie	· 1x RS-232C IN (D-9 connector) · 1x RS-232C OUT (D-9 connector) · 1x RS-232C IN (XLR connector) · 1x 2way prop. protocol to Rugged remote (5 pins XLR connector) · 2x prop. protocol (RJ45 connector) · mini-jack for wired remote control
Compatibiliteit	· All current video sources (PAL, SECAM, NTSC) in Composite, S-VHS, Component or RGB formats · All currently proposed HDTV, extended and improved television standards (1080i; 720p) · All computer graphics formats from VGA, SVGA, XGA, SXGA,full HD to UXGA · Most Macintosh computers · Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz · Most computer sources with a pixel clock up to 200 MHz · DVI sources up to DC2K (2048x1080)
Compatibiliteit invoerbron	max. input: up to 2048 x 1080 and 1600 x 1200
Schermmaat	From 1-16m and higher / 3-52ft.recommended
Scanfrequenties	Pixel clock >162Mhz (UXGA 60hz)
Netwerkverbinding	Standard (10/100 base-T; 2 ports; internal HUB)
Geïntegreerde beeldschermserver	Ethernet control standard remote control projector over ethernet via Projector Toolset
Omgevingstemperatuur	Max 35°C (95°F)
Lamp	6.0 kW Xenon Lamp warranty: 750 hrs
Lenzen	Fixed focal lenses Lens Order nr XLD 1.0 R9852950 Zoom lenses Lens Order nr XLD 1.45 -1.8 R9852090 XLD 1.8 -2.4 R9852092 XLD 2.2 -3.0 R9852094 XLD 2.8 -5.5 R9852100 XLD 5.5 -8.5 R9852920

Product specificaties**XLM H25**

Lensverschuiving	Vertical: -10% to +110% Horizontal: -50% to +50% (small differences occur per lens type)
Lens-encoders	On zoom and focus (with XLD lenses)
Projectieverhouding	Fixed focal lenses Lens Throw ratio XLD 1.0 1.0 Zoom lenses Lens Throw ratio XLD 1.45 -1.8 1.45 -1.80 XLD 1.8 -2.4 1.80 -2.40 XLD 2.2 -3.0 2.20 -3.00 XLD 2.8 -5.5 2.80 -5.50 XLD 5.5 -8.5 5.50 -8.50
ScenergiX	Standard horizontal and vertical electronic edge blending
Verzegelde DLPT™-kern	Standard
Stoffilters	Metal filters
Geluidsniveau	64 dBA (at 40°C)
Netspanning	3 x 400 V + N or 3 x 220 V
Energieverbruik	8000 W
Vermogensdissipatie	max 23906 BTU/h
Wisselstroom	190V -255V (50 Hz -60Hz)
Gewicht	180 kg (400 lbs)
Afmetingen	WxLxH 810 x 1563 x 631 mm (31.9 x 61.5 x 24.8 inch)
Veiligheidsvoorschriften	Compliant with UL1950 and EN60950
Elektromagnetische storing	Complies with FCC rules & regulations, part 15 Class A and CE EN55022 Class A
Bestelgegevens	R9010100 (Projector incl. 4 inputs) R9010101 (Projector incl. 1 DVI) R9852410 (Spare Lamp) Fixed focal lenses Lens Order nr XLD 1.0 R9852950 Zoom lenses Lens Order nr XLD 1.45 -1.8 R9852090 XLD 1.8 -2.4 R9852092 XLD 2.2 -3.0 R9852094 XLD 2.8 -5.5 R9852100 XLD 5.5 -8.5 R9852920

Laatst bijgewerkt: 15 Mar 2023

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.