


LDX-46

46" full HD LED backlit LCD display



Barco's LDX-46 display with LED backlights has been designed for use in a wide variety of professional applications. The LDX-46 produces crisp, bright and color-accurate images on a 46" screen size.

Featuring LED backlit LCD technology, the LDX-46 boasts a high brightness and durable LED backlight technology and provides an exceptionally thin and space-saving design. Available in native full high definition (1920 x 1080 pixels), the LDX-46 is a high-quality display for long-term usage.

Barco's LDX-46 combines the typical benefits of liquid crystal technology (such as low maintenance costs) with energy-efficient LED backlights, reducing image burn-in and colorations.

Wide viewing angle

The wide viewing angle (178°) and large surface are very beneficial in collaborative environments where detailed information is viewed by multiple participants.

Space-saving design

The LDX-46 is based on Edge LED technology, meaning that the LEDs are positioned around the outer rim of the screen. This technology provides the LDX-46 with an exceptionally thin and space-saving design. The display has been designed for easy installation of high-quality standalone applications or as a complementary visualization solution in modern control rooms.

High resolution

Barco's high-resolution LDX-46 shows large amounts of data in accurate and high-quality images. Any input source can be shown pixel-on-pixel, which avoids unnecessary scaling artifacts often found on lower-resolution displays. Combined with the displays' non-glossy professional LCD panel and Anti-Image Retention functionality, the LDX-46 delivers bright and crisp images that do full justice to high-resolution graphics and video.

Product specifications**LDX-46****General specifications**

LCD technology	S-PVA, normally black DID technology for extensive usage AIR Anti Image Retention Circuitry
Resolution	Full HD (1920x1080)
Backlight	Edge LED
Aspect ratio	16:9
LCD technology	<ul style="list-style-type: none">• S-PVA, normally black• DID technology for extensive usage• AIR Anti Image Retention Circuitry• Internal 10bit processing for precise color calibration
Pixel density	48 dpi
Refresh rate	120 Hz
Luminance	700 cd/m ² (max)
Contrast ratio	4000:1 (typ)
Viewing angle	H 178°/ V 178°
White point	10,000 K
Color depth	10 bits -1.07 B colors
Precision	Internal 10bit processing for precise color calibration
Backlight lifetime	50,000 h
MTBF	> 100,000 h @25°C
Active screen diagonal	46" (1168 mm)
Dimensions	1075 x 639 x 85 mm (42.32" x 25.16" x 3.35")
Active screen area	1019 x 573 mm (40.12" x 22.56")
Weight	27 kg (59.52 lbs net)
Cooling	Fanless cooling -low noise
AC input voltage	100-240 VAC, 60-50Hz
Power consumption	207W (max) 88 (typ) 19 (sleep) 2.1 (stdby)
Heat dissipation	706 BTU/h (max)
VGA	Separate sync DSUB-15P in/out
DVI	Single link DVI-D in/out with HDCP
DisplayPort	Display port input (Out via DVI)
HDMI	HDMI Type A with HDCP (Out via DVI)
HD-SDI	2x BNC in 2x out SD, HD, 3Gb/s
CVBS	BNC in/out
S-video	Mini-DIN S-terminal in/out
Component video	3xBNC in/out
Barco NSL control manager	Server connected via RS232 chain Remote client application: on/off, wall setup, source selection, status, brightness, contrast and color adjustments
Control signal	RS-232 DSUB9 PIN in/out
Operating temperature	0° to 40°C
Operating humidity	20-80% non-condensing
Storage temperature	-20 -60°C
Storage humidity	10-90% non-condensing
Regulation Compliance	CE, TÜV, cTÜVus, CCC, ROHS, WEEE

Last updated: 08 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.