

iQ6-W6

ISO 6,000 lumens, WUXGA, 3 X LCD laser phosphor projector



LCD
PROJECTION

LASER PHOSPHOR

6K
LUMENS

- **Brilliant image**
- **Flexible installation**
- **Barco service & support**

The iQ6 series expands Barco's projector product portfolio to offer users with high resolution and vivid colors. Thanks to a variety of correction functions, large lens shift, and 1.6X high magnification lens enable possibilities for convenient and rapid installation and wider applications, while providing valuable Barco services and support.

A new generation of laser light source, with high efficiency and low energy consumption, the laser modular design leads to improve the utilization of laser source and avoid the risk of sudden failures in important demonstrations. The four set of adjustable laser control extends the lifetime up to 20000 hours. Thanks to high heat resistance WUXGA inorganic LCD panel to offer constant vivid colors. With contrast optimization function on allows you access to high-resolution up to 3,000,000:1

Flexible installation

It supports correction functionalities as Keystone, 4-corner/6-coner, pillow/barrel distortion, multi-point, with 1.6X zoom lens functionality and the maximum lens shift range of 60% (upward) vertical direction and $\pm 29\%$ in the horizontal direction, and Configures on 360 ° all-round installation function which ensure fast and convenient installation.

Barco Services & Support

With iQ6 series, you can enjoy Barco's mind of peace service. The laser light source not only guarantees good image quality, but also has lower maintenance costs than most lamp projectors on the market.

Product specificaties**IQ6-W6**

General specifications	
Type projector	3 X LCD laser phosphor projector
Resolutie	1,920 x 1,200 (WUXGA) -0.64" LCD
Helderheid	6,000 ISO lumen*
Contrastverhouding	3,000,000:1 (Contrast optimization ON)
Helderheidsuniformiteit	85% (Typical)
Beeldverhouding	16:10
Type lens	iQ6 LENS (1.2-2.0 : 1) Manual
Optische lensverschuiving	iQ6 LENS (1.2-2.0 : 1) Manual: H±29% V 0%, +60% Manual zoom and focus Manual lens shift
Kleurcorrectie	No
CLU (constante lichtuitvoer)	No
Lichtbron	Laser phosphor
Levensduur laser	20,000hrs
Oriëntatie	360° rotation, no restrictions
3D	No
Beeldverwerking	Embedded warp
Trapeziumcorrectie	Yes
Invoer	HDMI IN 1.4 x 2 /VGA IN x 1/VGA OUT x 1/ AUDIO IN x 1/AUDIO OUT x 1
Invoerresoluties	Up to 1,920 x 1,200 @ 60Hz/3,840 x 2,160 @ 30Hz
Controle	IR, RS232, RJ45
Netwerkverbinding	10/100 Ethernet, RJ45
Voedingsvereisten	100-240V / 50-60Hz
Energieverbruik	350W (full normal) /240W(Eco1) / 220W(Eco1)
Stroom in stand-by	less than 0.5W(ECO)
Geluidsniveau (standaard bij 25°C/77°F)	37dB(full normal) / 29dB(Eco1) / 27dB(Eco1)
Bedrijfstemperatuur	0~40
Opslagtemperatuur	-10~50
Vochtigheid in bedrijf	20%-85%
Vochtigheid bij opslag	10%-85%
Afmetingen (B x L x H)	405mm x 373mm x 137mm
Gewicht	7.9KG
Standaardaccessoires	Power cord, wireless remote control
Certificeringen	CCC/CECP/CELWEEE/China Rohs
Garantie	3 years or 20.000hrs runtime, whichever comes first; 5 years or 20.000hrs as an option * Measurement, measuring conditions, and method of notation all comply with ISO/IEC 21118: 2012 international standards * ISO21118: The lower-limit values of the projector must maintain 80% of the values in specification sheets for the brightness

Laatst bijgewerkt: 11 Mar 2024

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.