

Retrodata 708 50"



技术规格**RETRODATA 708 50"****一般规格****兼容性**

Horizontal autolock scan frequency of 15-69 kHz
Vertical scan frequency of 37-210 Hz
RGB bandwidth of 75 MHz
A wide range of PC graphics boards with a resolution up to 1280 x 1024 pixels/60 Hz
Universal input signal connection facilities

光输出

2000 Nit/582 ftL.
176 Nit/52 ftL. (Economy mode)
234 Nit/69 ftL. (Normal mode)
277 Nit/81 ftL. (Boost mode)

屏幕尺寸

50"

生成于: 08 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可, 禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新, 信息和技术规格如有变更, 恕不另行通知。请查看www.barco.com.cn以了解最新规格。