


VRWF-3200

Network-centric VR workroom display for stereoscopic data analysis and decision-making



Product specifications

VRWF-3200

General specifications

Projector	2x iCon H600, side-by-side ceiling mounted
Resolution	HDTV (1920 x 1080 pixels)
Active screen height	1.8m (70")
Active screen width	3.2m (125")
Lens	QHD 1.4 -2.1
Inputs	Standard: <ul style="list-style-type: none">■ 2x Composite Video (BNC)■ 2x S-Video (4-pin mini-DIN)■ 1x DVI■ 1x VGA (D15 connector)■ 2x 5-BNCs capable of connecting■ Video over IP■ Audio: microphone and line-in (mini-jacks) Optional: <ul style="list-style-type: none">■ Extension with extra video input (Composite and S-Video)■ Extension to SDI and HD-SDI
Network connection	The integrated display server allows easy integration in a network infrastructure.
Picture-in-picture	Up to 4 external sources
Control	The VRWF-3200 workroom display can be powered up or down by means of RS232.

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.