

# RLM H5 Performer

With its compact design and sealed optics, the RLM G5 Performer has proven itself to be an ideal all-round projector suitable to both the rental and staging markets.



**Product specifications****RLM H5 PERFORMER**

General specifications	
Light output	4500 ANSI Lumen
Resolution	1280 x 720 (native)
Contrast ratio	1000 : 1 (full field)
High contrast mode	Available with special lenses
Brightness uniformity	> 90%
Lamp	2 x 250 W mercury max. lifetime: 1500 hrs typ. lifetime: 1000 hrs min. lifetime: 750 hrs
Noise level (@ 20°C -68°F)	42 dBa
Noise level (@ 40°C -104°F)	46,5 dBa
Ambient temperature	Max 40°C (104°F)
Power consumption	700 W
Mains Voltage	92-240 V
Weight	Projector: 25 kg (56 lbs) Frame: 5 kg (11 lbs)
Dimensions (WxLxH)	705 x 707,8 x 316,5 mm
Light shutter	Standard
Sealed DLP™ core	Standard
ScenergiX	Standard horizontal and vertical electronic edge blending
Seamless Switching	Standard (wipes, fades, ...)
Picture-in-picture	Up to 4 sources simultaneously (2 data, 1 video and 1 SDI)
Digital zoom	Standard
Lens encoders	On zoom and focus (with TLD lenses)
Linked Constant Light Output	not available
Input source compatibility	1600 x 1200 (max. input)
Fixed Inputs	<ul style="list-style-type: none"><li>■ 1x configurable 5 cable (BNC)</li><li>■ 1x composite Video (BNC)</li><li>■ 1x S-Video (4-pin DIN)</li><li>■ 1x analogue RGB (D15 Connector)</li><li>■ 1x SDI/HDSDI ( + loop-through)</li><li>■ 1x DVI (Digital Visual Interface)</li></ul>
Modular inputs	not available
Control	· 1 x RS-232 / 422 IN · 1 x RS-232 / 422 OUT · 1 x XLR female (2 way) · build-in RF remote transceiver (optional)

**Product specifications****RLM H5 PERFORMER**

Shift Range	Lens	Shift Range
	RLD 0.8	up-down: 35<>35 left-right: 15<>15
	Other RLD	up-down: 130<>40 left-right: 50<>50
	TLD (HB) 0.8	up-down: 90<>50 left-right: 40<>40
	Other TLD (HB)	up-down: 140<>50 left-right: 50<>50
Throw Ratio	Lens	Throw ratio
	RLD 0.8	0.64
	RLD 1.5 - 1.8	1.2 - 1.44
	RLD 1.8 - 2.25	1.44 - 1.8
	RLD 2.25 - 3.0	1.8 - 2.4
	RLD 3.0 - 4.5	2.4 - 3.6
	RLD 4.5 - 7.0	3.6 - 5.6
	TLD (HB) 0.8	0.8
	TLD (HB) 1.6 - 2.0	1.6 - 2.0
	TLD (HB) 2.0 - 2.8	2.0 - 2.8
	TLD (HB) 2.8 - 5.0	2.8 - 5.0
	TLD (HB) 5.0 - 8.0	5.0 - 8.0
Order Information	R9010300	

Last updated: 15 Mar 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.