

MICA

All-in-one Transportable Passive Stereo Solution



技术规格

MICA

一般规格

兼容性	<ul style="list-style-type: none">· All current video sources (PAL, SECAM, NTSC) in composite, S-VHS, RGB or component formats· All currently proposed HDTV, extended and improved TV standards
双重兼容	Active stereo sources with minimum 1024 x 768 @96Hz to maximum 1280 x 1024 @120 Hz
光输出	<ul style="list-style-type: none">· 2 x 3,400 ANSI lumens with BarcoReality SIM 6 mkII
液晶面板	3 active matrix poly-Si LCD panels resulting in an overall resolution of over 1.3 million pixels
对比度	500:1 (full white/full black)
镜头	QFD 1.27:1 lens
极化	<ul style="list-style-type: none">· Standard: linear polarized· Optional: circular polarized
屏幕尺寸	1678 x 1346 mm / 66.06 x 52.99 inch
移动性	Standard equipped with wheels to allow easy relocation and transportation
净重	Shipping weight: 337 kg
尺寸	Length: 2,332 mm / 97.81 inch Height: 2,170 mm / 85.43 inch Width: 2,183 mm / 85.94 inch
装运尺寸	Length: 766 mm / 30.12 inch Height: 1,590 mm / 62.60 inch Width: 2,183 mm / 85.94 inch

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。