

SLM R10 Performer

A Compact Projector for Rental & Staging Applications



技术规格**SLM R10 PERFORMER**

| 一般规格 | |
|----------------------|---|
| 光输出 | 10.000 ANSI Lumen |
| 数字微镜器件 | 3 high resolution SXGA DMD™s |
| 分辨率 | 1280 x 1024 (native) 1600 x 1200 (max) |
| 亮度均匀性 | 90 % |
| 对比度 | Normal mode: 800 : 1 High mode: 1600 : 1 (Full White/Full Black) |
| 灯泡 | Lifetime (max): 1000 Hrs Lifetime (typ): 500 Hrs Lamp power: 2,2 kW |
| 噪音级别(@ 20°C -68°F) | < 56 |
| 噪音等级 (@ 40°C -104°F) | < 58 |
| 电源电压 | 200-240 V |
| 功率消耗 | 2750 W |
| 环境温度 | 35°C (95 F) |
| 尺寸 | 875 mm x 585 mm x 429 mm 34,5" x 23" x 16,9" |
| 重量 (包括装备齿轮) | 57 kg (126 lbs) |
| 镜头 | BARCO's "click-and-play™" TLD lenses provide the highest quality picture. Available both in fixed and zoom versions. |
| 镜头移动 | Motorized V shift: up to 100% Motorized H shift: up to 65% |
| 封装DLP™内核 | No |
| 无缝切换 | Standard |
| ScenergiX | Standard |
| 网络连接 | Optional |
| 固定输入 | · 2 Multifunctional 5-cable inputs for the connection of RGB analogue signals with standard sync (BNC connectors) or tri-level sync, sync on green or separate sync, Standard Video signals, S-VHS signals · 2 Multistandard DVI · SDI input (Serial Digital Input) |
| 可选输入 | One free digital input slot for optional input modules: · SDI · HD -SDI |
| 远程控制 | · RS232 or RS422 loop-through input (D9-connector) for PC based projector control · Communication input (D9-connector) for peripherals · 3 pin male XLR connector for wired remote (standard remote) · 3 pin female XLR connector for bi-directional communication (rugged remote) |

生成于: 16 Mar 2023技术规格随时变化, 不会事先通知。请访问www.barco.com.cn, 获取更新信息。