

MUIP-2213

13.3" touch user interface



- Sealed fanless thermal design (IPx3)
- Easy-to-use with surgical gloves and drapes
- Excellent image quality from any angle
- Ultra-low power consumption
- Long lifetime availability
- High Quad Core performance
- Multiple connectivity options
- Ultra-low power consumption
- 'A' ecolabel for a sustainable choice

Unlock the potential of your medical workspace with the MUIP-2213, Barco all-in-one user interface device tailored to smarter control in the interventional suite, cathlabs, hybrid OR, or quickly and seamlessly integrated into a wide range of mobile imaging systems, treatment, and robotic surgical devices.

Seamless mobility and point-of-care treatment

- Support the demand for on-the-go applications across the hospital enterprise: it can be used in CathLab, Examination Rooms & Control Rooms, Surgical Rooms and Hybrid Operating Rooms, both inside and outside the patient area.
- Can be used for third party software applications that provide a user interface for medical systems.
- Can be desk, cart, arm, or boom mounted to accommodate a wide range of applications.

Excellent image quality and intuitive touch control

- High-brightness, excellent contrast ratio and its anti-glare front glass makes it ideal for brightly lit clinical environment.
- Easy-to-use with surgical gloves and drapes thanks to its P-CAP Multi-Touch technology.
- Easy-to-see and effortless control due to the MUIP's combined crisp image quality and wide viewing angle

Medical-Grade ITE Assurance

- Adheres to strictest medical-grade ITE standards and the latest design specifications.
- Sealed fanless thermal design with no ventilation holes eliminates any



- Sealed fanless thermal design with no ventilation holes eliminates any infection weak point.
- Its IPX3 rating protects against water, surgical fluids and contaminants and allows cleaning according to hospitals infection control guidelines.

Seamless integration and rapid validation

- Engineered according to the most rigorous protocols validation of MUIP-2213 into a medical device or system is quick and streamlined
- Easily connect to any medical device or system via Ethernet or USB cable for hassle-free communication.

Powered by an Intel Pentium N6415 Quad Core CPU, 8 GB RAM, and a 128 GB SSD drive provides high-performance coupled with ultra-low power consumption and multiple connectivity options for a longer useful lifetime.

Configure your MUIP-2213 with the following optional configurations:

- Extend the RAM up to 16Gb
- Additional SSD
- Integrated WiFi/BT
- Integrated RFID

Minimal order quantities apply.

Alternatively, Barco designs custom solutions from the ground up to deliver the exact performance you need. Visit <https://www.barco.com/en/products/medical-displays/custom-medical-displays> to learn how we help you to realize your custom medical project.

The equipment is not intended to be used for displaying medical images, nor for diagnostic purposes.

Product specifications**MUIP-2213****General specifications**

Size	13.3"
Type	a-Si TFT-LCD
Viewing Angle	+/-80° (minimum)
Luminance	400 cd/m ²
Resolution	1920x1080
Contrast Ratio	800:1 (typical)
Backlight	PLED
Touch Screen	PCAP multi-touch with 10 fingers (support gloves touch)
Software Driver	Windows
CPU	Intel Pentium N6415 Quad Core
System Memory	RAM: 8 GB
3D Graphics	Integrated Intel Graphic
Storage	SSD: 128 GB
Connectivity	I/O Interface I/O interface Specifications 2 x Gbps wired LAN (RJ45) 2 x USB 3.0 (USB type A) 1 x USB C (DC power IN, Video OUT) 1 x audio line OUT (3.5 mm Jack) 1 x DC power IN (Jack)
Power Input	12-24 V DC
Operating System -Primary	Windows 10 IoT
Audio Jack	1 x audio line OUT (3.5 mm Jack)
Color	Plastic housing RAL 9003
Mounting	75x75 mm VESA
Cooling	Fanless
Dimensions	334 mm X 226 mm X 38.8 mm
Weight	1.7 kg (without internal battery); 1.9 kg (with internal battery)
IP rating	IPX3
Operation Temperature	+10°C to 35°C (with battery); +0°C to 40°C (without battery)
Storage Temperature	-20°C to +50°C (with battery); -20°C to +60°C (without battery)
Package Drop	Follows ISTA 2A STD
Certifications	<p>Product Classification and Marks Product Classification: ITE Medical Grade</p> <p>AAMI ES60601-1:2005, ES60601-1:2005/AMD1 1:2012, ES60601-1:2005/AMD2:2021 CAN/CSA-C22.2 NO. 60601-1-14/A2:2022 IEC 60601-1:2005, AMD1:2012, AMD2:2020 EN 60601-1:2006/A1:2013/A12:2014/A2:2021 IEC 62368-1: 2018 EN IEC 62368-1:2020+A11:2020 IEC 60601-1-2: 2014 +A1:2020 EN 60601-1-2: 2015 +A1:2021</p> <p>EMI specific:</p> <p>FCC part 15 Class B ICES-003 Level B GB17625.1-2012; GB4943.1-2011; GB/T9254-2008</p> <p>Applied marks:</p> <p>Europe: CE (ITE), DEMKO US and Canada: UL, FCC, ICES-003 Japan: VCCI Australia: RCM China: CCC</p>
Accessories included in the packing	<p>Product Contents · Sealed Connector Cover</p> <ul style="list-style-type: none"> · AC/DC Power Adapter (IN 100-240VAC; OUT 19 VDC) (depending on the model) · EU Power Cord (depending on the model) · US Power Cord (depending on the model) · User Guide (English)
BIOS	Insyde BIOS
Optional accessories	Desktop stand Country specific power cords
Power Consumption	Less than 13 W (Display ON)
Warranty	3 years
Operating Humidity	10% to 90% non condensing
Storage Humidity	10% to 90% non condensing
Operating Altitude	70 Kpa to 110 KPa

Last updated: 12 Mar 2026

© 2026 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.