

LC40

40" LCD display with WXGA resolution.



Product specificaties

LC40

General specifications	
Actief schermgebied	862mm x 517mm (33.9" x 20.4")
Actief scherm (diagonaal)	1010mm (39.6")
Beeldverhouding	15:9
Helderheid	450NIT
Kleuren	16.8 million
Contrastverhouding	600:1
Controle	RS232 control On Screen Display (OSD)
Hor. kijkhoek	170°
Vochtigheid	Max. 85%
Invoerbereiken	RGB analog: Pixel clock : 20 .. 165 MHz Horizontal sync range : 15 .. 110 kHz Vertical sync range : 23 Hz .. 125 Hz Max input format = UXGA (1600x1200) @ 60 Hz DVI: Pixel clock : 25 .. 165 MHz Horizontal sync range : 15 .. 110 kHz Vertical sync range : 23 Hz .. 125 Hz Max input format = UXGA (1600x1200) @ 60 Hz SDI: SMPTE259M compatible serial digital signals only. CVBS/SVHS/Component video: PAL B, G, D, H, I and N, combination PAL N, PAL M, NTSC M, NTSC-Japan, NTSC 4.43 and SECAM. Video amplitude nominal 700mVpp for component signals 1Vpp with 300mVpp sync amplitude for composite and sync-on-Y signals.
Levensduur	typical 50.000h
Native resolutie	1280 x 768 (W-XGA)
Bedrijfstemperatuur	5°C to 40°C (41°F to 104°F)
Energieverbruik	270W (330W including Compact PC)
Voedingsvereisten	Input: 85V-264V (50Hz-60Hz)
Naleving van regelgeving	UL, CE
Standaardingen	DVI, RGBHV (on BNC), SDI
Technologie	TFT LCD
Vert. kijkhoek	170°
Gewicht	25kg / 55.1lbs

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

