

iQ Pro R200L



技术规格

IQ PRO R200L

一般规格	
光输出	1,800 ANSI lumen
亮度均匀性	>95 % for the total screen
对比度	>400 : 1 (full white/full black)
液晶面板	3 active matrix 1.3" diagonal XGA polysilicon LCD panels with Micro Lens Arrays and a resolution of 1366 x 1024 pixels (aspect ratio 4:3).
分辨率	1366 x 1024 (native)
网络	iQ Pro Server Specifications: -Processing Power: Pentium III socket with 1,2 Gigahertz Tualatin Celeron processor -Memory: 256 MB RAM -Storage: 40 GB hard disk -Video memory up to 64 MB -Inputs and outputs <ul style="list-style-type: none">▪ PCMCIA slot for Wireless LAN cards, memory cards, Bluetooth, input extensions ...▪ RJ45 connector for Ethernet (10Mb/s) and Fast Ethernet (100Mb/s)▪ 4 USB connectors▪ Audio: 3,5 mm jacks for Microphone in, Line in and Line out
特性	· Advanced picture-in-picture · Seamless switching with effects · Standard cable basket · Standard light shutter · Advanced digital zoom
兼容性	The iQ Pro R200L is compatible with: <ul style="list-style-type: none">▪ All current video sources (PAL, SECAM, NTSC) in Composite, S-VHS, Component or RGB formats▪ All currently proposed HDTV, extended and improved television standards (1080i, 720p)▪ All computer graphics formats from VGA, SVGA, XGA, SXGA to UXGA▪ Most Macintosh computers▪ Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz▪ Most computer sources with a pixel clock up to 160 MHz DVI sources up to SXGA
屏幕尺寸	From 1-6 m/3-20 ft.
输入	1x Configurable 5-Wire (BNC) for: Composite Video, S-Video, Component Video, RGBHV, RGBS, RGBS. 1x Composite Video (BNC) (up to 7 Composite Video's when using all connectors on top input board) 1x S-Video (4-pin mini-DIN) (up to 3 S-Video's when combining BNC's) 1x VGA (D15 connector) 1x DVI (Digital Visual Interface)
灯泡	2x 120 Watt UHP lamp, in lamp housing Typical lifetime: 6000 h/lamp. 6000 hours in Dual Lamp Mode or max. 12000 hours/set in Single Lamp Mode
镜头	Fixed focal length lenses are available with a throw ratio of 0.85:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 7.0:1 (long throw). Variable focus lenses with a throw distance of 1.3-1.8, 1.9-2.6, 3.0-6.0 times the screen width
扫描频率	Horizontal 15 kHz -110 kHz Vertical 25 Hz -150 Hz
镜头移动	V shift: -30% +120%
尺寸(宽x长x高)	Projector body with cable basket: 415 mm (Max W) x 195 mm (Max H) x 565 mm Projector body without cable basket: 415 mm (Max W) x 195 mm (Max H) x 487 mm (Max D)
净重	Net weight, body only: 12.9kg/28.5 lbs.
通信	1x D9 connectors for RS232 In/Out 1x spherical IR receiver
噪音级别	
电源	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
功率消耗	Max 380 Watt
功率消耗	Max 1297 BTU/h
安全级别	Compliant with UL1950 and EN60950
电磁干扰	BARCO's iQ Pro R200L complies with FCC rules & regulations, part 15 Class B and CE EN55022 Class B
无缝切换	Standard

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可, 禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新, 信息和技术规格如有变更, 恕不另行通知。请查看www.barco.com.cn以了解最新规格。