

RGB Laser ODL-721

Laser-lit rear-projection video walls for 24/7 control rooms



- **2x more brightness than mainstream LED-lit rear-projection video walls**
- **25% less power consumption at higher brightness levels**
- **More than 11 years of uninterrupted operation in 24/7 mode**
- **Unmatched colors, focus, and contrast levels**
- **Silent like never before ('library' noise level)**
- **Redundancy of critical components for ultimate peace of mind**
- **50% setup-time reduction (motorized 7-axis alignment)**

Powered with the latest laser technology, Barco's RGB laser rear-projection video walls delivers unseen brightness levels and vibrant colors, while offering a very low total cost of ownership (TCO). With its 10th generation of rear-projection video walls, Barco again raises the bar for critical infrastructure markets visualization.

Providing 2x more brightness than mainstream LED-lit rear-projection video walls, the RGB laser series take away all brightness issues of earlier video walls. Because the high luminance allows operating under daylight conditions, control rooms can finally light up - which improves operator working conditions! Adding vibrant colors to this mix, that make all nuances clearly distinguishable, you make sure nothing is wrongly interpreted and situational awareness is enhanced.

Over 11 years of uninterrupted 24/7 operations

With the RGB laser for 24/7 control rooms series, Barco takes another giant leap forward in terms of reliability. With a light source lifetime of at least 125,000 hours in both normal and eco-mode, and redundancy of all critical components (including power supply, inputs, and laser drivers), nothing is left to chance when it comes to uptime. Unlike technology used by competitors and in non-24/7 meeting rooms, Barco's RGB laser display series doesn't need a rotating color wheel to operate. Since each color can be uniquely controlled and is not dependent on the segment of a color wheel, it provides color control like never before and eliminates color breakup.

Automatic calibration and alignment

The engine of Barco's RGB laser for 24/7 control rooms is fully motorized. Installers and maintenance staff will never need to open up the individual modules to perfectly align the individual cubes of the video wall. Using a web interface, the video wall can be remotely aligned by a single technician - including keystone correction. This is far more efficient, more reliable, and less time consuming, saving up to 50% of alignment and adjustments efforts. Combined with the Sense X automatic calibration system, continuously measuring and adjusting brightness and color levels over the complete video wall, users are sure the complete canvas is perfectly balanced at any time.

Product specificaties**RGB LASER ODL-721**

General specifications					
Resolutie	Full HD (1920 x 1080 pixels)				
Contrast op scherm	1800:1				
Scherm	Screen type	WV-FEL	CSI	Light source lifetime (hrs)	Power usage (W)
	Boost	940 cd/m ²	650 cd/m ²	60,000	260
	Normal	730 cd/m ²	500 cd/m ²	125,000	200
	Eco	365 cd/m ²	250 cd/m ²	125,000	120
	Mid gain type, 180° viewing angle	-	-	-	-
Kleur	Up to 170% REC709 color triangle				
Weergavetechnologie	Rear projection DLP				
Wit punt	Customized white points				
Ruimte tussen schermen	Dependant on screen type				
Helderheidsuniformiteit	Typ. >95% ANSI 9 Typ. >90% ANSI 13				
Afmetingen	<ul style="list-style-type: none"> • Diagonal: 70" (Approx.) • Width: 1,550 mm 61.02" • Height: 872 mm 34.33" • Depth: 622 mm 24.49" • Weight: Projection Module: < 63 kg 139 lbs • Weight: Support frame: < 39 kg 86 lbs 				
Kleurstabiliteit	Sense X automatic calibration				
Redundantie	Redundant laser banks with redundant power supply drivers, input signal & external power supply				
Lichtbron	RGB lasers illumination (Lasers Class 1 RG2)				
Ingangsspanning (wisselstroom)	100 – 240 VAC, 50-60Hz				
Levensduur lichtbron	> 125,000 hrs in both Normal and Eco mode				
Geluidsniveau	Less than 20 dB (measured from 3 meters in front)				
Vermogen	120W (eco) 200W (normal)				
Connectiviteit	2x DP1.2 inputs & 1x output (4K@60Hz) 2x HDMI 2.0 inputs (4K@60Hz) 2x USB ports (only for power) 2x Ethernet ports				
Gebruiksomstandigheden	10°C-40°C 50°F-104°F Up to 80% humidity (non-condensing)				
Warmtedissipatie	390 BTU/h (eco) 680 BTU/h (typ) 860 BTU/h (max)				
Integratie met apparatuur van derden	WEB service API				
HDCP	2.2 compliance				
Signaalverwerking	Loop through Cropping, scaling with wall configuration				
Directe Ethernet-toegang	Built in web server				
Grafische gebruikersinterface	All settings and operational parameters				
Garantie	2 years				
Opmerkingen	⁽¹⁾ In general, rear projection video walls have no bezels, only a mechanical gap which depends on video wall configuration and operating temperatures				

Laatst bijgewerkt: 16 Apr 2024

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.