

# Duet

Active-to-Passive Stereo Converter for BarcoReality SIM 6



## 技术规格

## DUET

### 一般规格

视频输入	<ul style="list-style-type: none"><li>· RGB: 0.4 – 2 Vpp @ 75Ω and gain = 1</li><li>· Composite or separate sync: TTL level (buffered loop-through) @ 20 kΩ load or analog (direct loopthrough) 0.3 to 5 Vpp</li><li>· The D9 female connector provides the ID-bits for the recognition of the graphical mode. (When no monitor is connected, the mode can be set through ID bits on the interface)</li><li>· Automatic 75Ω termination</li></ul>
输入分辨率	<ul style="list-style-type: none"><li>· XGA 60-120 Hz</li><li>· SXGA: 60-120 Hz (reduced blanking) 60-108 Hz (standard blanking)</li></ul>
立体输入	<ul style="list-style-type: none"><li>· Stereo signal between -12/+12 V</li><li>· Supported connectors are: MiniDIN p3m, MiniDIN p7m, DB9 (male and female), BNC (other connectors available on request)</li></ul>
视频输出	<ul style="list-style-type: none"><li>· RGB Analog 0.4 – 2.5 Vpp @ 75Ω and gain = 1</li><li>· Output sync selection between composite or separate sync</li><li>· HD15 loop through feature</li></ul>
带宽	Typical 200 MHz @ 0.7 Vpp in / 0.7 Vpp out [-3dB]
兼容性	<ul style="list-style-type: none"><li>· The Duet works only with projectors featuring "Active Stereo Compatibility", such as: BarcoReality SIM 6, BarcoReality SIM 6 HB, BarcoReality SIM 6 LL, BarcoReality SIM 6 HB MLA, BarcoReality SIM 6 Ultra, Warp 6TM</li><li>· The Duet is compatible with most switching devices and 3D graphics cards. For an up-to-date list of incompatible devices please check your local Barco office.</li></ul>
电源	Built-in power supply for operation on 240 – 100 VAC.
功率消耗	20 Watts
安全级别	The Barco Duet complies with UL 1950 and EN60950
电磁干扰	The Duet complies with FCC part 15 Class A
架座	Mounting holes on the cabinet facilitate wall or rack mounting of the interface.
净重	Shipping 5,8 Lbs. 2,634 Kg Duet 1,9 Lbs. 0,842 Kg Cables 1,6 Lbs. 0,719 Kg
尺寸(宽x长x高)	9.69 x 4.69 x 2.24 Inch 246 x 119 x 57 mm
装运尺寸	15.95 x 10.83 x 8.27 Inch 405 x 275 x 210 mm

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看[www.barco.com.cn](http://www.barco.com.cn)以了解最新规格。