

G62-W9

9,000 lumens, WUXGA, DLP laser phosphor projector



- **Great image quality**
- **Optimal integration capabilities**
- **4K compatible and 3D-ready**
- **Guaranteed service and support**

The G62-W9 expand the single-chip offering with a quality WUXGA projector of 9.000 lumens. It opens up the possibilities to a wider range of applications while still relying on the valued Barco service and support.

The laser phosphor light source ensures great image quality, on the one hand, but also lower maintenance compared to most lamp-based projectors on the market. Thanks to Barco's Projector Toolset software, installing and managing your projector(s) can be done from the comfort of your own computer.

The G62 models enable HDMI 2.0 input capabilities and higher bandwidth than its predecessors, which makes them 4K compatible and 3D capable to visualize your high-quality content at its best.

The projectors are available in black and fully white chassis, allowing you to choose the perfect fit for your specific environment. Their uniform compact size, the compatibility with other Barco products and the wide lens shift range enlarge the projectors flexibility.

Product specifications**G62-W9****General specifications**

| | |
|------------------------------------|--|
| Projector type | Single chip DLP laser phosphor projector |
| Technology | 0.67" |
| Resolution | 1,920 x 1,200 (WUXGA) |
| Brightness | 8,000 ANSI lumens 8,900 center lumens 9,500 ISO lumens |
| Brightness uniformity | 90% |
| Contrast ratio | 1,200:1 sequential; 6,000:1 dynamic; Extreme black: 750,000:1 |
| Light source | Laser phosphor |
| Light source lifetime | Up to 20,000hrs |
| Aspect ratio | 16:10 |
| Orientation | 360° rotation, no restrictions |
| Sealed DLP™ core | Yes |
| Color correction | Yes |
| CLO (constant light output) | Yes |
| Image processing | Embedded warp & blend possible via Ptoolset |
| 3D | Active stereoscopic 3D |
| Lens type | G-lenses -0.36:1 / 0.37-0.4:1 / 0.65-0.75:1 / 0.75-0.95:1 / 0.95-1.22:1 / 1.22-1.53:1 / 1.52-2.92:1 / 2.90-5.50:1 |
| Optical lens shift | Vertical up to 100%, depending on lens Horizontal up to 30%, depending on lens Motorized zoom and focus Motorized lens shift |
| Inputs | 2x HDMI In (version 2.0) (with locking screw) / 1x DVI-D (only support digital signal) / 1x HDBaseT / 1x 3D SYNC In / 1x 3G-SDI |
| Input resolutions | Up to 4K @60Hz Refresh rates: 24Hz to 60Hz for WUXGA and 4K/4KUHD (4096 x 2160 / 3840 x 2160) 4K input signals will be scaled to the projector's output resolution |
| Software tools | Projector Toolset |
| Control | 1x RS232, 3.5mm phone jack for wired remote |
| Network connection | 10/100 Ethernet, RJ45 |
| Power requirements | 100-240V / 50-60Hz |
| Power consumption | 625W nominal, 750W maximum |
| Standby power | less than 0.5W |
| BTU per hour | 2,133 BTU/h nominal; 2,252 BTU/h maximum |
| Noise level (typical at 25°C/77°F) | 36dB(A) -40dB(A) depending on the used mode |
| Operating temperature | 0 ~ 40 °C (sea level) |
| Operating humidity | 10 -85% RH, non-condensing |
| Storage temperature | -10 ~ 60 °C |
| Storage humidity | 5 -90% RH, non-condensing |
| Dimensions (WxLxH) | without feet: 484 x 529 x 195 mm / 19.1 x 20.8 x 7.7 inch with feet: 484 x 529 x 206 mm / 19.1 x 20.8 x 8.1 inch |
| Weight | without lens: 17.4 kg / 38.4 lbs |
| Standard accessories | Power cord, wireless remote control |
| Certifications | CE, FCC Class A, cTUVUS, CCC, EAC, KCC, RCM, BIS, BSMI |
| Warranty | Limited 3 years parts and labor |

Last updated: 30 May 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.