

DP2K-15C

Compact DLP Barco Alchemy Cinema projector (14,500 lumens)



- Small footprint, budget-friendly performance
- Integrated, DCI-compliant projector
- Combines media server functionalities with Series 3 cinema processing electronics

The Barco Alchemy DP2K-15C is a compact and fully integrated digital cinema projector for mid-size theaters based on Texas Instruments' 0.98" DLP Cinema® chip. It ensures a first-class movie experience with consistent picture brightness, rich contrast and vibrant colors. By merging the projector and media server functionalities into one projector module, the Barco Alchemy DP2K-15C is a full-fledged, DCI-compliant projector and media-server solution with on-board storage. Reducing the required hardware, it increases simplicity and reliability. Truly smart, it detects potential operational errors and warns users about mishaps. Great in TMS environments, it operates stand-alone in single-screen applications. Thanks to the embedded Barco Web Commander user interface, shows can be created and scheduled remotely.

Low cost of ownership

Geared with the integrated Barco Alchemy technology that drives operational and maintenance costs down, the DP2K-15C offers superior image processing, DCI quality images and ultimate reliability at a low TCO.

Easy maintenance and operation

The DP2K-15C comes with the 'Barco Web Commander' screen management system featuring an intuitive user interface. The projector detects potential operational errors and warns users in case of mishaps. It also has a fully modular architecture for simple serviceability and higher uptime.

The DP2K-15C projector can be ordered without the Barco Alchemy module.

Unique benefits of Barco Alchemy technology

- Combines media server functionalities with cinema processing electronics

- Fewer boxes lead to more reliability and ease-of-use
- Simple operation thanks to intuitive 'Barco Web Commander' user interface
- Easy upgrading of Series 2 projectors with Barco Alchemy module
- Budget-friendly solution with minimal cost of ownership thanks to integrated Barco Alchemy technology, re-usable filters, low maintenance, etc.
- Includes storage
- Maximum ease-of-use through intuitive 'Barco Web Commander' screen management system, running via a web browser
- Barco Communicator for simple configuration and updates of all modules in the projector
- Consistent image quality and brightness thanks to the proprietary sealed engine and advanced DMD cooling
- Easy installation and maintenance thanks to proven modular design and shared components with the other Barco DP2K B-series projectors

Product specificaties

DP2K-15C

General specifications

Digital MicroMirror Device™	3 x 0.98" DC2K dark metal devices
Native resolutie	2,048 x 1,080 pixels
Behuizing	Hermetically sealed DMDs and optical assembly
Lamp	1.2kW -3kW
Lichtuitvoer	14,500 lumens
Schermaformaat	Up to 15m / 49ft wide (screen gain 1.4 @ 14 ftl)
Contrastverhouding	2,000:1
Primelencen	1.2 -1.8 1.4 -2.05 1.6 -2.5 1.95 -3.2 2.4 -3.9
I/O-controle	3x Ethernet 8x GPIO (DB 25) 3D interface USB RS-232 interface (DB9)
Integrated Cinema Media Processor	DCI 4K 2D up to 60fps* DCI 4K 3D (24 or 30 fps per eye)* DCI High Frame Rates 2K 3D up to 120fps (60fps per eye) JPEG 2000 bit-rates up to 625Mbps Dual-channel color-correction MPEG-2 (4:2:0 and 4:2:2 up to 60fps) 2x Displayport 2x 3G-SDI inputs 1x HDMI 1.4a (up to 4K 2D 24fps, support for BluRay 3D) 16x AES/EBU audio channels (2x RJ45) 8x GPI, 8x GPO (4x RJ45) 2x Gbe for content connectivity & ingest 2x front-accessible USB 3.0 for fast ingest 2x front-accessible USB 2.0 Video watermarking: Civolution NexGuard Audio watermarking: Civolution Closed captioning devices: Support for SMPTE 430-10 * 4K 24fps is standard. For 4K 60 fps / 4K 3D on ICMP upgrade modules a license is required. Newly-built 4K Barco Alchemy projectors have the license standard included.
Geïntegreerde opslag	1.9TB effective storage (RAID-5) / 3x 1TB Hot-swappable 2.5" hard-drives 3.9TB effective storage (RAID-5) / 3x 2TB Hot-swappable 2.5" hard-drives
Barco Web Commander	Projector Dashboard Projector Control Board Show Player/Editor/Scheduler Automation, 3D, Ingest Dynamic DCP playlists & intermission TMS integration Smart Projector Status Via HTML5 web-browsers including iOS & Android tablets Dual projector 3D: passive and active Auro 11.1 decoding
Barco Communicator	Projector installation & configuration Projector update & maintenance
Projectordiagnose	via Integrated Media Server via Communicator control software via SNMP agent
Voedingsvereisten	220V
Afmetingen	558(H) x 694(W) x 1034(D) mm 22.0(H) x 27.3(W) x 40.7(D) inch NB.: min. 5 cm of air inlet spacing required at the bottom of projector
Gewicht	102kg (225lbs)
Omgevingstemperatuur	35°C / 95°F Max.
Luchtuitstroom	240 – 280 cfm (6,8 – 8 m³/min)
Veiligheidsvereisten	Class 1 risk group 3
Opties	3D add-ons Touch screen monitor, inc. Barco Commander & Communicator Pedestal CineCare Web Auro 11.1 license Barco Escape license Live 3D*** ** In testing *** Software roadmap

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.