


DP4K-20LHC

High-contrast 6P RGB laser cinema projector for premium screens



- **Exceptional image quality for white and silver screens**
- **Very high contrast and high brightness**
- **Simplified operations**
- **Reduced operating expenses**

The 6P RGB LHC range doubles the contrast of the L-series flagship laser projectors to provide Premium Large Format (PLF) screens with an even more significant improvement in image quality. Now you can choose between higher contrast or higher brightness within Barco's flagship laser cinema projector range.

Unprecedented image quality

With a contrast ratio of 6,000:1 and brightness levels of 17,000 lumens, the DP4K-20LHC significantly boosts contrast while still providing a high brightness level for mid-size premium screens. The DP4K-20LHC offers the same superior color saturation and uniformity as the other flagship laser projectors.

Simplified operations

Fully integrated, the DP4K-20LHC greatly reduces complexity. It not only frees you from all lamp-related costs and maintenance, thanks to the single projector setup you can also seamlessly integrate it into your current system. In this way installing and operating the projector also becomes easier and downtime is reduced. What's more, if you already own a DP4K-30L flagship laser projector from Barco you can upgrade it to a high-contrast version.

Reduced operating expenses

One major saving of the projector is that you avoid all lamp-related material, maintenance, and administrative costs. Thanks to its superior optical efficiency level, electrical costs are driven down as well. In this way, you can reduce your operating expenses.

Product specifications**DP4K-20LHC**

General specifications	
Brightness	17,000 lumens typical
Native contrast ratio	6,000:1 / 1,000:1 ANSI contrast (typical)
Prime lenses	1.13-1.72; 1.35-1.86; 1.46-2.10; 1.65-2.60; 2.00-3.35
Resolution	4,096 x 2,160
Long-term brightness stability	Less than 20% decrease during a runtime of 30,000 hrs
Dimensions (WxLxH)	Projector: 744 x 1,445 x 706 mm / 29.3 x 56.9 x 27.8 inches (with feet, no lens) One chiller with the following dimensions: 701 x 701 x 800 mm / 27.6 x 27.6 x 31.5 inches
Weight	Projector: 200kg (~440lb) Chiller: ~115kg (~250lb)
Cooling liquid hose length	2.5-5-10m (8.2-16.4-32.8ft)
Power requirements	Projector: 200-240/346-415V 50-60Hz 16A 3W+N+PE (Y connection) / Power cord size range: 4 sq mm to 6 sq mm, 10AWG to 8AWG / Circuit breaker range: 25A to 40A 200-240V 3W+PE 28A 50-60Hz (delta connection) / Power cord size: 6 sq mm, 8AWG / Circuit breaker: 40A Chiller: 230/400V 3W+N+PE 16A, 2.5 sq mm (Y connection) or 208V / 3W+PE (delta connection) / Max. 16A per phase
Ambient temperature	30°C (86°F) Max. (projector and chillers)
Ambient humidity	75% Max. (projector and chillers)
Power consumption	Projector @ full laser power: 3.5 kW (2D or Polarization 3D) / 2.0 kW (Barco Laser3D -6P) Chiller @ full laser power: 2.0 kW (2D or Polarization 3D) / 1.6 kW (Barco Laser3D -6P) Projector @ half laser power: 2.0 kW (2D or Polarization 3D) / 1.2 kW (Barco Laser3D -6P) Chiller @ half laser power: 1.6 kW (2D or Polarization 3D) / 1.2 kW (Barco Laser3D -6P)
Media server	Barco Alchemy ICMP included in the projector: <ul style="list-style-type: none">■ JPEG2000 2K & 4K DCI play-out■ High Frame Rates 3D up to 120fps (60fps per eye)■ 2x HDMI2.0a (up to 4K 2D 60fps)■ 2x 3G-SDI inputs■ 16x AES/EBU audio channels (2x RJ45)
3D systems	Color3D (Barco Laser3D): Native 6-primary color-3D system. Only requires color filter glasses (Dolby3D glasses cannot be reused) Active glasses systems Polarization recuperation systems
DCI	Projector + Barco Alchemy ICMP DCI CTP 1.2 certified
Safety class	Class 1, RG3
Certifications	CE; ETL/UL/FCC, CCC

Last updated: 15 Mar 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.