

# D320



技術仕様

D320

|       |                                                                                                                                                                                                                                                                                                                              |
|-------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 一般仕様  |                                                                                                                                                                                                                                                                                                                              |
| 入力    | 4 user defined inputs<br>Front accessible<br>Integrated video processing<br>Auto sensing, hot swappable<br>S-video, composite, YUV, RGB<br>SDI, HD-SDI, DVI up to UXGA                                                                                                                                                       |
| 互換性   | LED displays                                                                                                                                                                                                                                                                                                                 |
| 出力    | DVI-A, DVI-D, RGB                                                                                                                                                                                                                                                                                                            |
| 制御    | <div><div>・ Scaler<br/>4 input channels [Data-Video]<br/>fully scalable to desired output<br/>resolution</div><div>・ Z-order<br/>Instant modification of Z-order control,<br/>for each output window</div><div>・ Window positioning<br/>Intuitive positioning interface</div><div>・ Connectors<br/>RS 232 [RJ11]</div></div> |
| エフェクト | Anamorphic imaging<br>Chroma-keying [per input]<br>Alpha-keying [per input]<br>Z-order control<br>Windowing/ View ports                                                                                                                                                                                                      |
| 動作温度  | 0° <-> 45°                                                                                                                                                                                                                                                                                                                   |
| 電力    | 240W-480W<br>auto ranging 90-264V (50-60 Hz)<br>Connector: 3 pin IEC                                                                                                                                                                                                                                                         |
| 品番    | R9851570                                                                                                                                                                                                                                                                                                                     |

生成日:09 Jul 2024

© 2024 Barco nv.(C) Barco. All rights reserved. （無断転載を禁ず。） 書面による許可なく全部または一部を複製することは禁止されています。すべてのブランド名および製品名は、それぞれの所有者の商標、登録商標、または商号です。継続的な技術革新により、情報および技術仕様は予告なく変更される場合があります。最新の仕様についてはwww.barco.comをご確認ください。

