

OverView cPG67 (Atlas C4)

67" Display Wall system integrating 3-panel Poly-Silicon LCD technology with XGA resolution.



Product specificaties**OVERVIEW CPG67 (ATLAS C4)****General specifications**

Resolutie	XGA
Beeldverhouding	4:3
Kleuren	16.7 millions
Lamp	• 100 Watt lamp • operation time 8,000 hours (average)
Wisselstroom	95-230 VAC $\pm$ 10%, 50-60 Hz
Vermogen	140 W
Luminantie	130 cd/m ² 38 ftL
Helderheid	600 lumens
Contrast	250:1
Helderheidsuniformiteit	> 95%
Afmetingen structuur	• Diagonal 67" • Width 1368 mm / 53.86 in. • Height 1026 mm / 40.39 in. • Footprint 753 mm / 29.65 in. • Dept 897 mm / 35.32 in. • Socket heigth 614 mm / 24.17 in.
Naleving van milieuwetgeving	• Operating temperature: 17 °C -27 °C or 62 °F -80 °F • Humidity: recommended 40% -60%, non condensing Typical for stitched screens. Consult download for more info on screen modules.
Schermen	• high gain screens for high brightness and high contrast black screens for wide viewing angles • other screens on request • Download the brochure for more info on the principles and technologies

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

www.barco.com**BARCO**