


BarcoGraphics 1209s + Iris³



技术规格

BARCOGRAPHICS 1209S + IRIS³

一般规格

兼容性	Display compatibility up to 2500 by 2000 pixel workstations Horizontal scan frequency range of 15-135 kHz 120 MHz RGB amplifiers Universal signal connection facilities
对比度	>1000:1 (full white/full black)
光输出	1250 Lumen (at 10 % peak white) 195 Lumen (Economy mode) 240 Lumen (Normal mode) 270 Lumen (Boost mode)
屏幕尺寸	Min.: 2 m (6.6 ft.) Max.: 8.8 m (29 ft.)

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。