


Input Controller 16

Input Controller 16



- 16 fully configurable inputs One output 19 inch rack mount Standard equipped with Xlite Toolset, controlling software. Multipurpose device: both Daylight Display and Projection Arrange your sources onto your display through an intuitive interface. Scale and position all sources exactly how you want them. Overlay sources using advanced chroma-keying and alpha blending features. Process video and data in pure quality onto your display. Compatible with all standard image formats.

Technische Daten**INPUT CONTROLLER 16****Allgemeine technische Daten**

Eingang	16 user defined inputs Front accessible Integrated video processing Auto sensing, hot swappable S-video, composite, YUV, RGB SDI, HD-SDI, DVI up to UXGA
Kompatibilität	Barco Daylight Displays Projectors
Ausgang	DVI-A, DVI-D, RGB
Bedienung	· Scaler 16 input channels [Data-Video] fully scalable to desired output resolution · Z-order Instant modification of Z-order control, for each output window · Window positioning Intuitive positioning interface · Connectors RS 232 [RJ11]
Effekte	Anamorphic imaging Chroma-keying [per input] Alpha-keying [per input] Z-order control Windowing/ View ports
Betriebstemperatur	0° <-> 45°
Leistung	240W-480W auto ranging 90-264V (50-60 Hz) Connector: 3 pin IEC
Bestell-Information	R9851580

Generiert am: 09 Jul 2024

© 2024 Barco nv. Alle Rechte vorbehalten. Die vollständige oder teilweise Reproduktion ohne schriftliche Genehmigung ist nicht gestattet. Alle Markennamen und Produktnamen sind Marken, eingetragene Marken oder Handelsnamen ihrer jeweiligen Inhaber. Aufgrund fortlaufender Innovationen können sich Informationen und technische Spezifikationen ohne vorherige Ankündigung ändern. Die neuesten Spezifikationen finden Sie unter www.barco.com.