


# LD140-10

Barco's LD LED display solution wraps all the desirable LED qualities of brightness, dependability, long lifetime and low maintenance into an affordable package that meets all your requirements for dynamic digital



**Product specifications****LD140-10****General specifications**

Display size	diagonal: 142" W x H: 3136mm x 1729 mm (124" x 71") surface: 5,6 m <sup>2</sup> (60 ft <sup>2</sup> )
LED type	3-in-1 SMD
Pixel pitch	10 mm
Resolution	308 x 176
Brightness	1200 NIT 1000 NIT (display calibrated at 6500° K)
Hor. viewing angle	145° + (min 50% brightness)
Vert. viewing angle	145° + (min 50% brightness)
Lifetime	100.000h (typ. use) 45.000h (full white -half brightness)
Processing	+12 bit/color
Colors	68.7 billion
Refresh rate	400 Hz
Power consumption	2.240W (Avg) 8.960W (Max)
Temperature range	operating: 0° to 40°C (32° to 140°F) storage: -20° to 60°C (-4° to 140°F)
Cabinet dimensions	width: 3372mm (133") height: 2028mm (80") depth: 330mm (13")
Weight	620kg -1367lbs (excl. opt. mounting)
Image processing device	D2

**Last updated: 10 Jul 2024**

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.