


QDX-W45

41,000 lumens, WUXGA, 3-chip DLP laser phosphor large venue projector



- **Stunning experiences thanks to high-brightness images**
- **Next-gen Pulse electronics with more processing power**
- **Durable design for maximized ROI**
- **Access to Barco's cloud-based Insights Management Suite**

Designed to deliver brighter, sharper, and lighter projections with unmatched speed, the QDX ensures immersive visuals that captivate audiences while offering an impressive return on investment.

Unprecedented image quality

The QDX-W45 projector boasts ultra-high brightness capabilities of 41,000 lumens, providing clear and vibrant images in any setting. Enhanced by our patented Pulse electronics, enjoy ultra-fast processing and high bandwidth support up to 8K@60Hz or 4K@240Hz for smoother images and sharper pixels.

Maximized ROI

The QDX is the world's most compact and lightest projector in its category, with everything at hand to maximize your ROI. It integrates seamlessly with your existing Barco equipment, including rental frames, flight cases, and TLD+ lenses. Fully compatible with Barco's smart peripherals and software tools, it ensures maximum return on your investment.

High Reliability

Built for longevity, the QDX projector maintains its stunning brightness and image quality over time. Its modular design allows for easy maintenance, and its advanced air filter system ensures reliable performance even in the harshest environments.

Product specifications**QDX-W45****General specifications**

Notes	The specifications in this document are preliminary
Projector type	WUXGA 3-chip DLP digital projector
Technology	0.96" DMD™ x3
Resolution	1920 x 1200 (WUXGA)
Brightness	41000 center lumens*
Contrast ratio	Full field 2.200:1
Contrast ratio Barco DynaBlack®	20.000:1
Optical lens shift	Vertical: up to -150% to +130% (motorized) Horizontal: up to +/-50% (motorized) with lens memory on TLD+ lenses
Light source	Blue+Red laser phosphor with inorganic phosphor wheel
Brightness uniformity	95%
Light source lifetime	20000 hrs (100% power, DynaBlack® off)
Color correction	Yes
Optical dowser	Laser switching /optional external
Aspect ratio	16:10
Lens type	TLD+
Lens range	TLD+ : 0.37:1 ; 0.65-0.85:1 ; 0.8-1.16:1 ; 1.25-1.6:1 ; 1.5-2.0:1 ; 2.0-2.8:1 ; 2.8-4.5:1 ; 4.5-7.5:1 ; 7.5-11.5:1
Color space	REC 709 +
Orientation	360°
Sealed DLP™ core	Standard
Inputs	HDMI™ 2.1 (HDCP2.2 -HDR10)/ DP1.4 (HDCP 1.3) RJ45 Ethernet / RS232 / USB(5v) / 12V out/ BNC 3D sync in-out
Input resolutions	Including and up to: 4096 x 2160 @ 240Hz 3840 x 2400 @ 240Hz 7680 x 4320 @ 60Hz
Processing	Pulse electronics
Web browser	Yes
Picture-by-picture	Two sources simultaneously
CLO (constant light output)	Yes
DMX 512	Yes
Image processing	Embedded warp & blend
Keystone correction	Yes
Standby power	
Software tools	Pulse Toolset + Android app + iOS app + IMS
Control	DMX (optional), XLR wired (optional) + IR, RJ45, Wifi (optional), GSM (optional)
3D	Active eye wear 3D stereo formats: 1xHDMI™ 1xDP or Quad DP(optioN/AI) top/ bottomsequential multi pipe. 1920x1200 @ 120Hz
24/7 operation	Yes
BTU per hour	Max 11935 BTU/h
Operating temperature	0-40°C / 32°-104°F (reduce power > 40°C)
Optional Inputs	Quad DP1.2 // Fiber SFP // HDBaseT/ HDMI™/ Quad-3G/ 12G/ DMX/ remote CTRL // HDBaseT
Storage temperature	-10°C to 60°C
Operating humidity	0-80% (no condense)
Storage humidity	5 -90% RH
Network connection	10/100 base-T RJ-45 connection Wifi (opt)
Dimensions (WxLxH)	660 x 830 x 350 mm / 25.98 x 32.67 x 13.77 inches
Weight	79kg / 174 lbs
Shipping weight	91kg / 200 lbs
Power requirements	120-160V (reduced power)20A / 200-240V (+/-10%) 32A 50-60Hz
Power consumption	At 230v: 3200W typical/ 3500W max At 120v: 2200W typical/ 2300W max
Noise level (typical at 25°C/77°F)	52dB(A)
Shipping dimensions (WxLxH)	800 x 1200 x 660 mm / 31.49 x 47.24 x 25.9 " incl. palet
Safety class	Laser Safety Class: RG3 Class 2
Standard accessories	Power cord wireless / XLR wired rugged remote control
Certifications	Compliant with UL60950-1 and EN60950-1 complies with FCC rules & regulations part 15 Class A and CE EN55032 Class A Rohs
Warranty	3 years
*Note	* Brightness levels +/-10%

Last updated: 05 Feb 2025

© 2025 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.