

BarcoReality 912

Powerful, 12" CRT projector with unsurpassed brightness



- normal mode, economy mode for longer lifetime of the CRTs and boost mode for special applications
- 3200K, 4900 K, 6500K, 9300K or custom
- with stepless adjustments for both horizontal and vertical axis
- for stereoscopic projection

技术规格

BARCOREALITY 912

一般规格

| | |
|--------|---|
| 光输出 | ANSI lumen: <ul style="list-style-type: none">· Economy Mode: 350 lumens· Normal Mode: 410 lumens· Boost Mode: 500 lumens |
| 阴极射线管 | High brightness, ultra-high definition liquid cooled 12" electromagnetic focus CRTs |
| 镜头 | Ultra-high definition, fully color corrected, liquid cooled lenses |
| 屏幕尺寸 | Min.: 2.0 m x 1.8 m (6.6' x 5.9') Max.: 10 m x 7.5 m (32.8' x 24.6') |
| 扫描频率 | Horizontal: 30 -180 kHz autolock Vertical: 37 -240 Hz autolock |
| 更小逆程时间 | <ul style="list-style-type: none">· Horizontal: < 1.1 μs in range 90-180 kHz < 1.8 μs in range 30-130 kHz (switching point adjustable between 90 and 130 kHz)· Vertical: < 200 μs |
| 三原色带宽 | 180 MHz [-3 dB] |
| 水平线性 | < \pm 0.5 % distortion @ 1280 x 1024 (60Hz) with convergence on green option < \pm 1.5 % distortion throughout the full horizontal frequency range |
| 输入 | <ul style="list-style-type: none">· RGB or (Y, R-Y, B-Y) input on 5 BNC-connectors, with automatic sync detection and sync polarity, with sync on green or separate sync· RGB analog input on D9-connector, with automatic sync detection and polarity (optional D9-BNC adapter available) |
| 更大寻址能力 | 3,200 x 2,560 pixels |
| 电磁干扰 | The BarcoReality 912 complies with CE EN55022 class B |
| 功率消耗 | 1,100 W |
| 安全级别 | The BarcoReality 912 complies with UL 1950 and EN60950 |

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。