ClickShare CX-30

Seamless wireless conferencing for small to medium-sized meeting and conference rooms



- Interactive features: touchback, annotation and blackboarding
- Increased collaboration with 2 sources on screen
- Run video meetings from your laptop with Button or App
- 100% secure, encrypted and cloud-managed

ClickShare CX-30 enables wireless conferencing in medium-sized meeting spaces. When you walk into the meeting room, ClickShare automatically connects you to room devices like cameras, mics, speakers, sound bars and displays.

Start a meeting from your laptop within seconds, using your preferred video conferencing platform. Make hybrid meetings easy, with just one click on the ClickShare Button or the ClickShare App, both for employees and guests.



| Product specifications | CLICKSHARE CX-30 |
|---|---|
| ClickShare Base Unit dimensions | |
| Dimensions (HxWxD) | 34 mm x 135 mm x 135 mm |
| Power supply | Standard 110/220 V AC plug or USB-C (only Gen2) |
| Power consumption | Operational: 5-10W, 24W Max |
| Weight | 900 gr |
| General specifications | |
| Operating system | Windows 10 and higher macOS 11 (BigSur) and higher Android v11 and higher (ClickShare App) iOS 14 and higher (ClickShare App) |
| System requirements | For a smooth experience with Microsoft Teams or Zoom Minimum: Intel i3 dual-core processor / 8GB RAM / OS: Windows 10 latest build or Mojave latest build Recommended: Intel i5 4-core processor / 8GB RAM / OS:Windows 10 latest build or Mac OS latest build |
| Video outputs | 4K UHD (3840*2160) @ 30Hz. HDMI 1.4b or USB-C DisplayPort 1.2 (only Gen2) |
| Audio output | USB, HDMI |
| USB | 1 X USB-A, 1 X USB-C |
| ClickShare Buttons | 2 |
| ClickShare App | Desktop & Mobile |
| Native protocols | Airplay, Google Cast, Miracast |
| Maximum number of simultaneous connections (with Buttons and/or App) | 32 |
| Noise Level | Max. 25dBA @ 0-30°C Max. 30dBA @ 30-40°C |
| Authentication protocol | WPA2-PSK in stand alone mode WPA2-PSK or IEEE 802.1X using the ClickShare Button in network integration mode |
| Wireless transmission protocol | IEEE 802.11 a/g/n/ac and IEEE 802.15.1 |
| Reach | Max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit Frequency band 2.4 GHZ and 5 GHz (DFS) |
| Frequency band | 2.4 GHZ and 5 GHz (DFS channels supported in select number of countries) |
| Connections | 1x Ethernet LAN 1Gbit 1x USB-C 2.0 (front); 1x USB-A 2.0 (front) -only Gen2: 1x USB-C 3.0 (front); 1x USB-A 3.0 (front) |
| Temperature range | Operating: 0°C to +40°C (+32°F to +104°F) Max: 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F) |
| Humidity | Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing |
| Anti-theft system | Kensington lock |
| Certifications | FCC/CE |
| Touch screen support & Interactivity | Yes |
| Wireless conferencing | via App or Button |
| Local view | Yes |
| Network connection | LAN & WiFi |
| Management and reporting | Yes |
| Warranty | 1 year standard. 5 years coverage via SmartCare |
| | |

Last updated: 05 Mar 2024

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.

BARCO