

BARCOVision 9200



技术规格**BARCOVISION 9200****一般规格****兼容性**

All current video sources in composite, S-VHS, RGB or Component forms
All currently proposed HDTV, extended and improved television standards
All computer graphics formats up to VGA (640x480) resolution
Computer signals in S-VGA (800x600) resolution
All Macintosh computers in 640x480 resolution

对比度

>180:1 (on 5x4 B/W checker board)
> 340:1 (full white/full black)

光输出

6000 Lumen Full White
5000 ANSI Lumen

屏幕尺寸

Min.: 1.0 m x 0.75 m (3.3' x 2.5')
Max.: 15 m x 11.25 m (50' x 37.5')

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可, 禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新, 信息和技术规格如有变更, 恕不另行通知。请查看www.barco.com.cn以了解最新规格。