

E-3620

3MP Medical Flat Grayscale Display



Product specifications**E-3620****General specifications**

Technology	TFT AMLCD Dual Domain IPS
Native resolution	2048 x 1536
Pixel pitch	0.207 mm
Active screen diagonal	528 mm (20.8")
Active screen width	423.9 mm
Active screen height	318 mm
Viewing angle	170° (10:1 contrast)
Dark room contrast	typical 900:1
Luminance	<ul style="list-style-type: none">500 cd/m2 Calibrated700 cd/m2 Max
Light output stabilization	Backlight Output Stabilization (BLOS®)
Digital Video Input	DVI connector
Operational temperature	0°C to +40°C
Within specifications	+15°C to +35°C
Safety	<ul style="list-style-type: none">CEUL1950CSA (or CUL) 950IEC 950
Emission	<ul style="list-style-type: none">EN55022 limit AFCC class AEN 61000-3-2

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.