

SLM G5 Performer

A Compact and Smokeproof Projector for Rental & Staging Applications



- Enhanced low-light video performance is the result of its newly designed pixel map processor.
- Integrated Constant Light Output (CLO), which can be linked with other G5 projectors for use in multi-screen applications.
- True seamless switching includes transition effects such as cross-fade, wipe, etc.
- Carrying handle with integrated rigging system.
- The unique "click-and-play" lenses make it possible to exchange lenses in seconds.
- Direct stacking and interlocking design enable an easy and stable setup
- Sealed optics significantly reduce optical system maintenance, which allows the G5 to be used at events where smoke generators are involved.
- Modular structure provides greater accessibility to serviceable parts.
- The optical system's compact and lightweight lens range is designed for the continuing evolution of the DLP technology.

Product specificaties**SLM G5 PERFORMER**

General specifications	
Lichtuitvoer	5.000 ANSI lumens
Resolutie	1024 x 786 (native) 1600 x 1200 (max)
Resolutie	1024 x 786 (native) 1600 x 1200 (max)
Digital MicroMirror Device™	3 high resolution XGA DMD's
Helderheidsuniformiteit	> 90% for the total screen area
Contrast	500:1 (full white/full black) 500:1 (full white/full black)
Lamp	Lifetime (max): 1500 Hrs Lifetime (typ): 1000 Hrs Lamp Power: 1,2 kW
Geluidsniveau (bij 20°C -68°F)	< 43
Geluidsniveau (bij 40°C -104°F)	< 50
Netspanning	110/230 V
Energieverbruik	1.600 W
Omgevingstemperatuur	40°C (104F) max
Grootte	875 mm x 585 mm x 429 mm 34,5" x 23" x 16,9"
Gewicht (inclusief takeluitrusting)	56 kg / 124 lbs
Lenzen	BARCO's "click-and-play!" TLD lenses provide the highest quality picture. Available both in fixed and zoom versions.
Lensverschuiving	Motorized V shift: up to 118 % Motorized H shift: up to 65 %
Verzegelde DLPT™-kern	Yes
Naadloos schakelen	Standard
ScenergiX	Standard
Vaste ingangen	<ul style="list-style-type: none">• 2 Multifunctional 5-cable inputs for the connection of RGB analogue signals with standard sync (BNC connectors) or tri-level sync, sync on green or separate sync, Standard Video signals, S-VHS signals• 2 Multistandard DVI• SDI input (Serial Digital Input)
Optionele ingangen	One free digital input slot for optional input modules: <ul style="list-style-type: none">• SDI• HD -SDI
Afstandsbediening	<ul style="list-style-type: none">• RS232 or RS422 loop-through input (D9-connector) for PC based projector control• Communication input (D9-connector) for peripherals• 3 pin male XLR connector for wired remote (standard remote)• 3 pin female XLR connector for bi-directional communication (rugged remote)

Laatst bijgewerkt: 15 Mar 2023

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.