

Barco Optix Cinemascope



The Barco Optix Cinemascope projector takes the exceptional 2.37:

1 native DLP chipset used in the Barco Orion Cinemascope to the next level.

This higher resolution required our optical engineers to develop all new optics and lenses, custom designed with aspherical glass elements and enhanced low dispersion glass for the highest possible image quality, increased contrast, improved color saturation and, above all, excellent sharpness.

技術仕様

BARCO OPTIX CINEMASCOPE

一般仕様	
プロジェクタータイプ	single chip DLP® projector LVDS DMD™ with DC4 DMD™
解像度	2560x1080
光出力	Up to 4,500 lumens
コントラスト比	Up to 8,000 : 1
レンズ群	"0.61 : 1 (EN47), 0.8 : 1 (EN 42), 0.75 -1.13 : 1 (EN45 & EN46) 1.2 -1.7 : 1 (EN 43), 1.7 -2.5 : 1 (EN41), 2.5 -4.6 : 1 (EN 44)"
光学レンズシフト	adjustable: vertical and horizontal, depending on lenses
ランプ	2 x 300W UHP VDI
ランプ寿命 (標準)	Up to 2,000 hours (Full power) / Up to 2,500 hours (Eco mode)
ランプを装着した搬送	yes
シールドエンジン	standard
互換性	"HDTV (1080p, 1080i, 720p), EDTV (576p, 480p), SDTV (576i, 480i), NTSC, PAL, SECAM, progressive scan"
3D	"active eyewear (optional), 2x optix cinemascope(stacked): INFITEC EX® 3D and Active Stereo IR, RF models, DLPLink™ "
入力	"2 x DVI-I, 2 x HDMI 1.3a, 2 x VGA 1 x Component, 1 x S-video"
制御	"1 x RJ-45 TCP/IP, 1 x 9-pin D-SUB RS232, 2 x 12V programmable trigger (3.5mm mini jack), 1 x Wired Remote 3.5mm mini jack, 2 x USB AMX Device Discovery, Crestron Certified Partner"
電源	8.4A ~100-240V 50-60Hz, typical consumption: Max 815W@100V
消費電力	630W
動作温度	10 -40 °C
動作湿度/結露なし	20 -80% RH
BTU消失	less than 3,109
設置	table top, ceiling mount, straight down or up.
寸法 幅×長さ×高さ	510 x 376 x 223 mm excluding lens
重量	12.7 kg, shipping weight 20 kg
梱包サイズ	780 x 520 x 370 mm (WxHxD)
ハウジング・カラー	black and white
証明書	CCC, cCSAus, FCC Class A, cUL, UL and CE
保証	"limited 3 years warranty. Up to five years extended warranty available. Conditions apply."

生成日:09 Jul 2024

© 2024 Barco nv.(C) Barco. All rights reserved. (無断転載を禁ず。) 書面による許可なく全部または一部を複製することは禁止されています。すべてのブランド名および製品名は、それぞれの所有者の商標、登録商標、または商号です。継続的な技術革新により、情報および技術仕様は予告なく変更される場合があります。最新の仕様についてはwww.barco.comをご確認ください。

