

E-2620

2MP Medical Flat Grayscale Display



Product specifications**E-2620**

General specifications	
Technology	TFT AMLCD Dual Domain IPS 8 bit/sub-pixel
Native resolution	1600 x 1200
Pixel pitch	0.249 mm
Active screen diagonal	498 mm (19.6")
Active screen width	398.4 mm
Active screen height	298.8 mm
Viewing angle	170° (10:1 contrast)
Dark room contrast	typical 850:1
Luminance	<ul style="list-style-type: none">■ 500 cd/m2 Calibrated■ 700 cd/m2 Max.
Light output stabilization	Backlight Output Stabilization (BLOS®)
Digital Video Input	DVI connector
Operational temperature	0°C to +40°C
Within specifications	+15°C to +35°C
Safety	<ul style="list-style-type: none">■ CE■ UL1950■ CSA (or CUL) 950■ IEC950
Emission	<ul style="list-style-type: none">■ EN55022 limit A■ FCC class A■ EN 61000-3-2

Last updated: 15 Mar 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.