

# DLite 7

The BARCO DLite 7 is the high resolution, indoor & outdoor LED display for various applications.



## 技术规格

## DLITE 7

### 一般规格

视觉分辨率	7,0 mm
物理分辨率	14,0 mm
亮度	6500 NIT 5000 NIT (calibrated @ 6500°K)
LED配置	2R, 2G, 1B
像素密度	20.407/m <sup>2</sup> (1.898/ft <sup>2</sup> ) 4.096/tile
水平观察角度	120° (min.50% brightness)
垂直视角	60° (min.50% brightness)
寿命	50 000 h (full white -half brightness)
功率消耗	maximum: 250 W / Tile average: 62 W / Tile
重量 / 层数	14 Kg / 30,8 lbs (excluding structure)
处理	color : +10 bit
颜色	1,07 billion
刷新率	400 Hz minimum (PAL / NTSC)
温度范围	operating : -20°C -40°C (-4 -104°F) storage : -20°C -60°C (-4 -140°F)
湿度	operating: 10 -99% storage: 10 -99%
D320输入能力	S-Video -Composite -YUV -RGB -SDI -HDS DI -Data DVI up to UXGA
认证	UL -CE -TUV -FCC Class A
瓦状尺寸	width: 448mm (17.6") height: 448mm (17.6") depth: 195mm (7.7")

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可, 禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新, 信息和技术规格如有变更, 恕不另行通知。请查看[www.barco.com.cn](http://www.barco.com.cn)以了解最新规格。