

NH-12

Network-centric, 1080p HD, 12,000 lumens three-chip DLP projector



Product specifications**NH-12****General specifications**

Light output	12,000 center lumens (+/-10%)
Contrast ratio	2,000:1
Resolution	Full 1080p HD
Chip type	Three-chip DLP
Lamp	2kW xenon
Lamp lifetime (typical)	750h warranted, max. 1000h
Weight	70kg (154.2lbs) net / 85kg (187.4lbs) shipping weight
Lens range	<ul style="list-style-type: none">Horizontal shift up to +/- 65%Vertical shift up to +/- 100%
Standard inputs	<ul style="list-style-type: none">1x 5-BNC (RGBHV, RGBS or RGBsB)1x composite video (BNC)1x S-video (4-pin mini DIN)1x DVI1x VGA (D15)
Optional Inputs	<ul style="list-style-type: none">SD/HD-SDI output
Communication Port	<ul style="list-style-type: none">RS-232 (on D9)IR or wired remote10/100 Mb/s Ethernet (on RJ45)
Video	<ul style="list-style-type: none">PAL, SECAM and NTSC signalsComposite, S-video, component or RGB formatsAll current HDTV standards (720i, 720p, 1080i, 1080p)
Data	<ul style="list-style-type: none">All computer graphics formats up to QXGA at 75HzAnalog sources with a pixel clock of up to 270MHzDVI sources with a pixel clock of up to 165MHz
Safety	<ul style="list-style-type: none">ETL60950 and EN60950CE compliantCCC compliant
AC power	200 -240 VAC / 50-60Hz
Max. power consumption	2,800 Watt / 9,560 BTU
Special Features	<ul style="list-style-type: none">Keystone and linearity correctionOptional full geometry correctionSealed, liquid-cooled engineDesktop output including external source windows on DVI-D

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.