

NH-12

Network-centric, 1080p HD, 12,000 lumens three-chip DLP projector



Product specifications**NH-12**

General specifications	
Light output	12,000 center lumens (+/-10%)
Contrast ratio	2,000:1
Resolution	Full 1080p HD
Chip type	Three-chip DLP
Lamp	2kW xenon
Lamp lifetime (typical)	750h warranted, max. 1000h
Weight	70kg (154.2lbs) net / 85kg (187.4lbs) shipping weight
Lens range	<ul style="list-style-type: none">▪ Horizontal shift up to +/- 65%▪ Vertical shift up to +/- 100%
Standard inputs	<ul style="list-style-type: none">▪ 1x 5-BNC (RGBHV, RGBS or RGBsB)▪ 1x composite video (BNC)▪ 1x S-video (4-pin mini DIN)▪ 1x DVI▪ 1x VGA (D15)
Optional Inputs	<ul style="list-style-type: none">▪ SD/HD-SDI output
Communication Port	<ul style="list-style-type: none">▪ RS-232 (on D9)▪ IR or wired remote▪ 10/100 Mb/s Ethernet (on RJ45)
Video	<ul style="list-style-type: none">▪ PAL, SECAM and NTSC signals▪ Composite, S-video, component or RGB formats▪ All current HDTV standards (720i, 720p, 1080i, 1080p)
Data	<ul style="list-style-type: none">▪ All computer graphics formats up to QXGA at 75Hz▪ Analog sources with a pixel clock of up to 270MHz▪ DVI sources with a pixel clock of up to 165MHz
Safety	<ul style="list-style-type: none">▪ ETL60950 and EN60950▪ CE compliant▪ CCC compliant
AC power	200 -240 VAC / 50-60Hz
Max. power consumption	2,800 Watt / 9,560 BTU
Special Features	<ul style="list-style-type: none">▪ Keystone and linearity correction▪ Optional full geometry correction▪ Sealed, liquid-cooled engine▪ Desktop output including external source windows on DVI-D

Last updated: 15 Mar 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.