


TruePix TP1.2-E

중간 밝기의 애플리케이션을 위한 1.2mm 픽셀 피치의 고해상도 실내용 LED 디스플레이



- **진정으로 매끄러운 결과를 보장하는 스마트 엔지니어링**
- **24시간 연중무휴 원활하고 효율적인 운영**
- **모든 조명 조건에서 탁월한 색상 정확도**
- **환경에 미치는 부정적 영향 감소**
- **최대 5년 동안 전담 서비스 및 지원**

TruePix TP1.2-E는 Barco의 새로운 플래그십 실내 고해상도 LED 플랫폼입니다. 화면 비율이 16:9인 27.5인치 타일의 픽셀 피치는 단 1.2mm에 불과합니다. TruePix는 제어실, 기업 및 방송 시각화 애플리케이션을 위해 설계되었으며, 주변 광원에 노출된 환경과 제어된 조명 환경을 모두 지원합니다.

진정으로 이음새 없는 이미지

TruePix는 수십 년의 경험을 바탕으로 LED 비디오 월 경험의 새로운 표준을 제시합니다. 이 솔루션은 스마트 엔지니어링과 Infinipix®의 차세대 기술인 Infinipix® Gen2를 결합하여 의도한 대로 콘텐츠에 생명을 불어넣고, 예측 가능하며 진정으로 매끄러운 이미지를 보장합니다. 24시간 연중무휴로 원활하고 효율적인 운영이 보장되므로 안심하고 사용할 수 있습니다.

Barco TruePix의 스마트 엔지니어링은 위험이 없고 정확한 설치를 위해 독특한 기계적 개념을 도입하여 시각적 왜곡을 제거합니다. 이 타의 추종을 불허하는 매끄럽고 평탄한 화면은 가이드 모듈 배치와 셀프 레벨링 마운트를 통해 달성됩니다. Barco의 독자적인 Infinipix® 처리 기술의 차세대 버전인 Infinipix® Gen2는 모든 밝기 수준에서 탁월한 색상 정확도와 완전한 이미지 무결성을 보장합니다. 눈의 피로를 줄여 주면서 모든 콘텐츠 요건을 유연하게 자동으로 지원합니다.

언제나 안심하고 사용

중단 없는 데이터 흐름을 통해 원활하고 효율적인 운영이 24시간 연중무휴 보장됩니다. 사용자는 EcoPower 대기 모드를 사용하여 탄소 배출을 줄일 수 있습니다. 전체 제품 수명 동안 안심할 수 있도록 최대 5년의 전담 서비스 및 지원(균일한 시정 환경 보장)을 제공합니다.

기술 사양**TRUEPIX TP1.2-E**

LED tiles	
Pixel pitch	1.27
Pixel per module	480x270 (HxV)
Aspect ratio	16:09
LED lifetime	100,000h (video -50% brightness)
Brightness	>600 nit
Peak brightness	780 nit
Internal processing	23 bit
Color depth	16 bit (281 trillion colors)
Shaders	No
Control	Infinpix® Gen2
Refresh rate	3,840 Hz
3D	3D supported
Frame rate	24 / 25 / 29.97 / 30 / 47.95 / 48 / 50 / 59.94 / 60 / 100 / 119.88 / 120 / 144 Hz
Hor. viewing angle	160° +/-5°
Vert. viewing angle	160° +/-5°
Brightness uniformity	>98%
Dimming	0-100%
Contrast	>7,000:1
Power consumption	714 W/m ² (max) 149 W/Tile 237.6 W/m ² (typ) 50 W/Tile
Heat dissipation	2,432 BTU/h/m ² (max) 810 BTU/h/m ² (typ)
Ceiling configurations supported?	Yes
Heat dissipation front/back	54%/46%
Operation power voltage	AC power: 100-240V 50/60Hz DC power: Input: 36-55Vdc 16A (max.) Output: 36-55Vdc 10.72A/36V (max.) or 12.55A/55V (max.)
Operational humidity	10 -80%
Operational temperature	-10°C to +40°C / 14°F to 104°F
Storage temperature	-20°C to +50°C
TAA Compliancy	Not available
Storage humidity	13 -85%
IP rating	IP30
Redundancy	Power: Optional Standard on REM tiles Data: Inter-tile and signal loop redundancy embedded / N + N redundancy optional
HDR	HLG / HDR10 supported

기술 사양**TRUEPIX TP1.2-E**

Concave curvature	Up to 5° standard curved tile (7m radius) Up to 5° curved modular tile (3.5m radius)
Convex curvature	Up to 3° standard curved tile (12m radius)
Ceiling configurations supported?	Yes
Dimensions	(WxHxD) 609.92x343.08x71mm / 24.01"x13.5"x2.80"
Weight	Standard / curved tile: 8.3kg/tile (single PSU) / 8.7kg/tile (dual PSU) / 8.2kg/tile (REM PSU) Modular curved tile: 9.1kg/tile (single PSU) 9.5kg/tile (dual PSU) / 9.0kg/tile (REM PSU)
Serviceability	Full front & full back service Modular curved tile -Full front & full back service (PSU only back access)
Cable management	No external cabling
Installation	Self-leveling with surface tolerance compensation
Module replacement	Automated parallel motorized extraction
Module placement	Guided module placement
Ergonomics	SteadyView™ driver algorithm to reduce eye fatigue
Certifications	CE, UL, FCC class A, RoHS, WEEE, REACH, CCC, RCM
TAA Compliancy	Not available
Warranty	3 years
EssentialCare Service offering	5 years with LED batch compatible modules

작성일: 09 Apr 2024기술 사양은 예고 없이 변경될 수 있습니다. 최신 정보는 www.barco.com에서 확인하십시오.