

# Versa® TUBE v2

Linear LED tube



**Product specifications****VERSA® TUBE V2****General specifications**

Resolution	36 pixels/meter
Colors	Over 1 billion (30-bit)
Light output	2,000 nits (cd/m <sup>2</sup> )
Lens	Diffused
Control	Versa DRIVE D3 or Versa DRIVE C1
Power	100-240VAC 50/60Hz
Power consumption	56W/meter
Dimensions	Length: 0.5 m (19.68 in.) or 1.0 m (39.37 in.) Width: 50.0 mm (1.97 in.) Height: 92.1 mm (3.62 in.)
Weight	2.4 kg/m (5.20 lbs.)

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.