

# 演示大师

PresentationMASTER™是一款专为系统集成商设计的音频/视频无缝切换台，可提供真正的无缝过渡。应用包括会议室、礼堂、教堂、会议室和教室。



一般规格	
A/V输入	<p>Universal A/V Inputs: (8) high bandwidth video channels</p> <p>High-Resolution Video: Supports conversion of RGB videos with horizontal scan rates up to 100 KHz and resolutions up to 1600x1200. HDTV 480p, 720p, and 1080i formats are supported in RGB colorspace. Input levels are independently programmable.</p> <p>Standard Video: Accepts RGB, YUV, S-Video (Y/C), or NTSC/PAL video formats. Input levels are independently programmable for RGB and YUV sources. Programmable luminance and chrominance levels are provided for S-Video, and Hue and Saturation controls are provided for NTSC/PAL inputs.</p> <p>Synchronization: The unit automatically locks to the incoming video source.</p> <p>Input Sync Signals: Sync-on-Video; Separate C or H,V</p> <p>Connectors: BNC</p>
视频输出	<p>High-Resolution RGB Video: User programmable output formats; VGA (640x480), SVGA (800x600), XGA(1024x768), SXGA (1280x1024), For plasma displays, 832x624, 848x480, 852x480, 1280x768, 1365x768, 1365x1024. Also provides HDTV 480p and 720p output rates.</p> <p>Main Outputs: Two independently buffered channels: (1) RGBHV with five BNC connectors; (1) RGBHV with HD-15 connector.</p> <p>Preview Output: (1) RGBHV with HD-15 connector</p> <p>Output Sync Type: Separate C or H/V</p>
音频输入	<p>Universal A/V Inputs: (8) stereo audio channels accept balanced and unbalanced inputs, 5-pin MCO Male connector</p> <p>Microphone Jack: MIC input, 3-pin MCO Male connector</p> <p>Line Input: LINE input, 5-pin MCO Male connector</p> <p>Audio Levels: Accepts Consumer or Professional signal levels</p> <p>Audio Mixing: MIC and LINE audio are mixed with audio from the selected A/V input</p>
音频输出	<p>Output: (2) stereo audio channels; Main and Preview each on 5-pin MCO Male connectors</p> <p>Audio Levels: Consumer or Professional signal levels</p>
用户控制	<p>Video Source Selection: (9) Illuminated keys support selection of 8 video inputs or black screen</p> <p>A/V Source Selection: (9) Illuminated keys support selection of 8 audio inputs or mute</p> <p>Audio Breakaway: Audio may be switched independently of video or set to video follow mode</p> <p>Audio Volume/Muting Control: Independent control for Master Volume, LINE Volume, MIC Volume and each of the eight A/V inputs for both Main and Preview outputs</p> <p>Video Transition Effects: Cut and Dissolve with programmable duration</p> <p>Set-up Controls: Electro-luminescent display, control knob, and 8 keys provide a menu-based front panel interface to simplify set-up.</p>
远程控制	<p>RS-232 port for real-time control; Optional external Ethernet (with TCP/IP and FTP) supports advanced real-time control, optional Multi-Screen Presentation Controller for control of up to 4 screens</p>
物理的	<p>Height: 5.25" (13.3 cm)</p> <p>Width: 17" (43.2 cm) or 19" (48.3 cm) with rear rackmount option</p> <p>Depth: 13" (33 cm)</p> <p>Weight: 22 lbs (10 kg)</p> <p>Shipping Weight: 30 lbs. (13.6 kg).</p>
输入电源	<p>85-264 VAC, 47-63 Hz, 1.75A max</p>
环境	<p>Temperature: 0-40 degrees C</p> <p>Humidity: 0-95% noncondensing</p>
保修期	<p>All video products are designed and tested to the highest quality standards and are backed by a full three-year parts and labor warranty.</p>

生成于: 06 Mar 2023

技术规格随时变化, 不会事先通知。请访问[www.barco.com.cn](http://www.barco.com.cn), 获取更新信息。