

Acsar 2

A powerful, yet extremely simple to operate scaler and router designed to convert any incoming signal to the DVI digital input of the D-Cine PREMIERE DP100 Digital Projector head.



Product specificaties**ACSAR 2****General specifications**

Video-ingangen	Modules: Hot plugable Slots: x 4; front panel insert, click and play -SDI -HD SDI -Analog composite video and -S-video with digital decoder (full standard PAL NTSC Secam) -DVI -RGsB / YUV video
Interne verwerking	16 bit
Uitgang	2048 x 1080 @ 24/50/60 Hz Preview output analogue RGB 2048 x 1080 @ 60Hz with OSD
Verbindingen communicatie-interface	Internal
Picture-in-Picture	4 x Picture in Picture windowing capabilities; any input, any size
Vermogen	Via projector Power Supply
Grootte	19" rack (w) x 1u (h) x 500 mm (d) with input modules
Standaardaccessoires	Barco RC5 Remote Control (supplied)
Gewicht	9.94 kg / 21.9 lbs fully loaded

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.